






REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	ECN-21-114380:ADD MATED CONDITION	31AUG2021	A.L	H.L

リール引出し方向
DIRECTION OFF TOP OF REEL




CONNECTOR DETAIL



SEE DETAIL F

カバーテープ
リッター部
外周一巻
WEEDING THE COVER TAPE
AROUND THE OUTER
PERIPHERY IN
A TURN.



NO	950	59.5	57.7	57.1	54.5	95	61.8	62.1	88	84.4	42.25	220	BLACK	△3-2040714-7
NO	950	59.5	57.7	57.1	54.5	95	61.8	62.1	88	84.4	42.25	220	BLACK	△3-2040714-6
SEALANT	QTY	T	S	P	N	W	E	D	C	B	A	POS.	HSG COLOR	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位: 耗 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差	DWN Y.NAKAZAWA 12MAR2008	TE Connectivity Ltd.
	0 PLC ± 0.3 1 PLC ± 0.3 2 PLC ± 0.3 3 PLC ± 0.3 4 PLC ± 0.3 ANGLES ± 0.3	CHK T.FUTATSUGI 12MAR2008	
MATERIAL 材料	FINISH 仕上	APVD T.FUTATSUGI 12MAR2008	NAME 名称 A
		PRODUCT SPEC 製品規格 108-5560	FH 0.5BTB CONNECTOR 220 POS REC 4H WITH G-CONT. AND CAP
		APPLICATION SPEC 取付適用規格	SIZE A3
		WEIGHT	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO 番号 G=2040714
			RESTRICTED TO
			SCALE 尺度 1:1
			SHEET 1 OF 3
			REV C1

4 3 2 1

© 2008 TE Connectivity. All Rights Reserved.

REVISIONS				
變更				
P	LTR	DESCRIPTION	DATE	DWN APVD
-	-	SEE SHEET 1	-	-

PLUG CONNECTOR
P/N: *-2040713-*

REC CONNECTOR
P/N: *-2040714-*

Ⓢ FULL-MATED CONDITION

⚠ MATERIAL; HOUSING: HIGH TEMP THERMO PLASTIC UL94V-0
CONTACT: COPPER ALLOY
SOLDER PEG: COPPER ALLOY

⚡ FINISH ; SIGNAL CONTACT: UNDER PL Ni 0.0013mm MIN ALL OVER.
CONTACT AREA 0.00076mm MIN Au PL.
SOLDERING AREA 0.00005mm MIN Au PL.

GROUND CONTACT: UNDER PL Ni 0.0013mm MIN ALL OVER.
CONTACT AREA 0.00076mm MIN Au PL.
SOLDERING AREA 0.00005mm MIN Au PL.

SOLDER PEG: 0.001mm MIN TIN PL. OVER
0.0013mm MIN Ni PL ALL OVER.

Ⓢ THIS POSITION IS GROUND CIRCUIT.

⚡ FINISH ; SIGNAL CONTACT: UNDER PL Ni 0.0013mm MIN ALL OVER.
CONTACT AREA 0.0002mm MIN Au PL.
SOLDERING AREA 0.00005mm MIN Au PL.

GROUND CONTACT: UNDER PL Ni 0.0013mm MIN ALL OVER.
CONTACT AREA 0.0002mm MIN Au PL.
SOLDERING AREA 0.00005mm MIN Au PL.

SOLDER PEG: 0.001mm MIN TIN PL. OVER
0.0013mm MIN Ni PL ALL OVER.


G-G
(GROUND POSITION)
(SCALE 8:1)

H-H
(SIGNAL POSITION)
(SCALE 8:1)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE TE Connectivity Ltd.	
		CHK		
DIMENSIONS: 單位: 耗 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差	APVD	NAME 名稱	EMBOSS ASSY FH 0.5BTB CONNECTOR 220 POS REC 4H WITH G-CONT. AND CAP
	0 PLC ± 0.3 1 PLC ± 0.3 2 PLC ± 0.3 3 PLC ± 0.3 4 PLC ± 0.3 ANGLES ± 3°	PRODUCT SPEC 製品規格	SIZE	
MATERIAL 材料	FINISH 仕上	APPLICATION SPEC 取付適用規格	CAGE CODE	DRAWING NO 番号
		WEIGHT	A3	00779
CUSTOMER DRAWING			G=2040714	RESTRICTED TO
			SCALE 尺度 4:1	SHEET 2 OF 3
			REV C1	

1470-19 (1/15)

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-



REFERENCE P.C. BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity Ltd.	
DIMENSIONS: 单位: 毫米 mm		CHK		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD	NAME 名称	
0 PLC ± 0.3 1 PLC ± 0.3 2 PLC ± 0.3 3 PLC ± 0.3 4 PLC ± 0.3 4 PLG ANGLES ± 0.3		PRODUCT SPEC 製品規格	EMBOSS ASSY	
MATERIAL 材料		APPLICATION SPEC 取付適用規格	FH 0.5BTB CONNECTOR 220 POS	
FINISH 仕上		WEIGHT	REC 4H WITH G-CONT. AND CAP	
		CUSTOMER DRAWING	SIZE A3	RESTRICTED TO
			CAGE CODE 00779	DRAWING NO. G=2040714
			SCALE 尺度 4:1	SHEET 3 OF 3
				REV C1