Thermofit Molded Parts Specification Control Drawing


Part Number : 204A011

Description : Boot, Coax Strain Relief

If this document is printed it becomes uncontrolled. Check with document control for latest revision.

NOTES

- 1. All dimensions are in $\frac{\text{incnes}}{[\text{millimeters}]}$
- 2. Dimensions appearing in table are as follows:
 - a As Supplied
 - b After Unrestricted Recovery
- Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max.






TABLE OF DIMENSIONS										
PART	н		J		Р	R	w			
NÜMBER	Min	Max	Min	Max	±10%	±10%	±25%			
	a	b	a	ь	b	b	ь			
204A011	.38 [9,6]	.31 [7,9]	.38 [9,6]	.08 [2,0]	1.12 [28,4]	.58 [14,7]	.04 [1,0]			

Raychem

RAYCHEM CORPORATION 300 CONSTITUTION DRIVE MENLO PARK, CALIFORNIA 94025

Revision: B

Date: 7/24/96

Part Number :

204A011

Description: Boot, Coax Strain Relief


Thermofit Molded Parts Specification Control Drawing

Part Number :

204A011

Description: Boot, Coax Strain Relief

COMPATABILITY CHART										
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.	COATING DESCRIPTION					
-3	Polyolefin, Semi-rigid	RT-301	/42	S-1017	Adhesive					
-4	Polyolefin, Flexible	RT-1304	/42	S-1017	Adhesive					
-6	Silicone	RT-602	N/A							



THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE; CONSULT YOUR NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION

Raychem

RAYCHEM CORPORATION 300 CONSTITUTION DRIVE MENLO PARK, CALIFORNIA 94025

Revision: B

Date: 7/24/96

Part Number :

Description: Boot, Coax Strain Relief

CAD FILE MP96517

204A011