

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC

	DIST
--	------

REVISIONS

GF

00

	F
--	---

LTR

DESCRIPTION

DATE _____

	DWN
--	-----

	APVD
--	------


B

REVISÉD PER ECO-10-024779

03/DEC/10

0|ECC

C	RB
---	----




PHYSICAL	—
CIRCUIT	16
MATING THICKNESS	0.32
STRIP LENGTH	5.00
REINFORCEMENT LENGTH	10.0
WIDTH	21.25
SPAN	18.75
MARGIN	0.85
CONDUCTOR WIDTH	0.80
CONDUCTOR THICKNESS	0.10
END THICKNESS	0.30±.05
TEMP	−50°C to 105°C
ELECTRICAL	—
VOLTAGE	90V
CURRENT	1.5A

1. NUMBER OF CONDUCTORS: 16
2. PITCH: 1.25mm
3. INSULATION: .002 INCHES THICK
POLYESTER FILM WITH FLAME RETARDENT ADHESIVE.
4. CONDUCTORS: .003" x .0315" ETP CU W/ ELECTROPLATED TIN FINISH.
5. UL RATINGS: AWM STYLE 20566, 105°C, 90V, VW-1
6. CURRENT: 1.5A PER TRACE
7. NO MARKINGS ON CABLE

MEETS REQUIREMENTS OF EU DIRECTIVE 2002/95/EC.

10	00000-009-51672	2053842-1
CUSTOMER REV	CUSTOMER P/N	TYCO ELECTRONICS P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E.C. CLAYBAUGH 24/MAR/10		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		CHK L. WIGBELS 24/MAR/10		CABLE ASSY, FFC, 16C, JUMPER, 1.25mm CL	
		APVD L. WIGBELS 25/MAR/10			
		PRODUCT SPEC —			
		APPLICATION SPEC —			
MATERIAL —		FINISH —		SIZE A3	CAGE CODE 00779
				DRAWING NO C-2053842	
				RESTRICTED TO —	
CUSTOMER DRAWING				SCALE N T S	SHEET 1 OF 1
				REV B	