


LOC		DIST		REVISIONS				
P	LYR	DESCRIPTION			DATE	DWN	APVD	
B1		REVISED PER ECO-14-018035			11MAR2015	AP	DD	
B2		REVISED PER ECN-24-252171			06MAR2024	AP	RS	

⚠ MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.

⚠ FINISH:
30µ" SELECTIVE GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.


3. CONNECTORS SUPPLIED WITH MOUNTING SCREWS.







SCALE 4:1

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

OBSOLETE	H	⚠	8-2057688-1
	G	⚠	7-2057688-1
	F	⚠	6-2057688-1
	E	⚠	5-2057688-1
	D	⚠	4-2057688-1
	C	⚠	3-2057688-1
	B	⚠	2-2057688-1
	A	⚠	1-2057688-1
NONE		⚠	2057688-1
KEY POSITION		FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. CARRO	05JAN2011	 TE Connectivity	IMPACT, 3 PAIR, DAUGHTERCARD 8 COLUMN, LEFT GUIDED, SIGNAL MODULE, 0.46 EYELET	RESTRICTED TO	
DIMENSIONS:	mm	CHK D. DIXON	05JAN2011				
		APVD D. DIXON	05JAN2011				
		PRODUCT SPEC					
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC			
		0 PLC ± 1 PLC ±0.2 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±		SIZE CAGE CODE DRAWING NO			
		MATERIAL		FINISH			
		SEE TABLE		WEIGHT			
		⚠		-			
				A100779C=2057688			
CUSTOMER DRAWING		SCALE 6:1		SHEET 1 OF 1			
				REV B2			



KEY POSITION CHART	
	NONE
	A
	B
	C
	D
	E
	F
	G
	H

RECOMMENDED PCB LAYOUT
MIN BOARD THICKNESS 1.0