





1.	THIS RCPT. IS DESIGNED TO CONFORM	TO	THE
	LATEST ISSUE OF MIL-C-24308		

- 2. MAX WIRE INSUL TO BE USED WITH THIS RCPT IS .068 DIA
- 3. STAINLESS STEEL RETENTION CLIPS ARE INCLUDED IN INSERTS
- 4. PACKAGE STAMPED M24308/2-293F
- 5. THIS RCPT. WILL ACCEPT SIZE 20 SOCKET CONTACT
- M24308/10 OR AMP # 205090
- AMP PART NO. STAMPED ON CONNECTOR REPRESENTS KIT NUMBER WITH CONTACTS

OBSOLETE	BRASS	205417-2	
	STEEL PER ASTM-A-109	205417-1	
	SHELL MAT'L	PART NUMBER	F

THIS DRAWING IS A C	CONTROLLED DOCUMENT.	C.C.THOMAS 12-10-87	TE Connectivity
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	FC BALLEW III APVD -	NAME
INCHES		_	RCPT. ASSY., AMPLIMITE, 15 POSN., SIZE 2
	0 PLC ± -	PRODUCT SPEC	SERIES 109,W/DUAL FLOATING BUSHINGS
\$	1 PLC ± - 2 PLC ± -	_	JEINES 103, W/ BONE 1 EOMINO BOSININOS
(4)	3 PLC ± .005	APPLICATION SPEC	_
_	4 PLC ± -		SIZE CAGE CODE DRAWING NO RESTR
MATERIAL	ANGLES ± -	WEIGHT	1 1 0 0 7 7 0 0 0 0 0 0 0 0 0 0 0 0 0 0
SEE CALLOUTS	SEE CALLOUTS	WEIGHT 0.00000	A 1 00779 C- 205417
		CUSTOMER DRAWING	SCALE 4.1 SHEET OF R