




LOC	DIST	REVISIONS			
P	LTN	DESCRIPTION	DATE	DWN	APVD
A		CREATED BY AUTOMATION PROGRAM	03JUN2011	RKC	JE



NOTCH DESIGNATES ROW A




- 1. MATERIAL:  
HOUSING: LCP, GLASS FILLED, UL94V-0.  
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2. FINISH:  
30µ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN ON PCB TAILS, NICKEL OVERALL.
- 3. FINISH:  
30µ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD ON PCB TAILS, NICKEL OVERALL.
- 4. SCREWS PACKAGED IN END OF PACKAGING TUBE.
- 5. FOR GROUNDED GUIDE PIN USE Ø3.56±0.08 PTH, Ø3.66 DRILL, AND Ø6.5 PAD.
- 6. KEYING PIN SHOWN IN POSITION A, SEE KEYING CHART ON SHEET 2 FOR OTHER POSITIONS.




Ø3.56±0.08  
Ø0.15  
UNPLATED SCREW HOLE

120X Ø0.39±0.05  
PLATED THRU HOLE  
120X Ø0.48±0.013  
DRILL HOLE  
Ø0.10

LEFT GUIDED  
BACKPLANE HOLE PATTERN  
(CONNECTOR SIDE)



1.4 TAIL LENGTH



1.00 MINIMUM BOARD THICKNESS


SECTION A-A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	03JUN2011	<b>STE</b> TE Connectivity
DIMENSIONS: mm		CHK	J. EARY 03JUN2011	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	J. EARY 03JUN2011	NAME IMPACT, 5 PAIR, 8 COLUMN, HEADER LEFT GUIDED, OPEN END WALL SIGNAL MODULE, 0.39 PTH
0 PLC ±		PRODUCT SPEC		
1 PLC ±0.25		APPLICATION SPEC		SIZE CAGE CODE DRAWING NO A100779C=2057769
2 PLC ±0.13		RESTRICTED TO		
3 PLC ±		WEIGHT		SCALE 5:1 SHEET 1 OF 2 REV A
4 PLC ±		CUSTOMER DRAWING		
ANGLES ±				
FINISH SEE TABLE				

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20  
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
AD	00	P	LTN	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1		-	-

3	H	5.5	8-2057769-6
3	H	4.9	8-2057769-5
3	H	4.5	8-2057769-4
2	H	5.5	8-2057769-3
2	H	4.9	8-2057769-2
2	H	4.5	8-2057769-1
3	G	5.5	7-2057769-6
3	G	4.9	7-2057769-5
3	G	4.5	7-2057769-4
2	G	5.5	7-2057769-3
2	G	4.9	7-2057769-2
2	G	4.5	7-2057769-1
3	F	5.5	6-2057769-6
3	F	4.9	6-2057769-5
3	F	4.5	6-2057769-4
2	F	5.5	6-2057769-3
2	F	4.9	6-2057769-2
2	F	4.5	6-2057769-1
3	E	5.5	5-2057769-6
3	E	4.9	5-2057769-5
3	E	4.5	5-2057769-4
2	E	5.5	5-2057769-3
2	E	4.9	5-2057769-2
2	E	4.5	5-2057769-1
3	D	5.5	4-2057769-6
3	D	4.9	4-2057769-5
3	D	4.5	4-2057769-4
2	D	5.5	4-2057769-3
2	D	4.9	4-2057769-2
2	D	4.5	4-2057769-1
3	C	5.5	3-2057769-6
3	C	4.9	3-2057769-5
3	C	4.5	3-2057769-4
2	C	5.5	3-2057769-3
2	C	4.9	3-2057769-2
2	C	4.5	3-2057769-1
3	B	5.5	2-2057769-6
3	B	4.9	2-2057769-5
3	B	4.5	2-2057769-4
2	B	5.5	2-2057769-3
2	B	4.9	2-2057769-2
2	B	4.5	2-2057769-1
3	A	5.5	1-2057769-6
3	A	4.9	1-2057769-5
3	A	4.5	1-2057769-4
2	A	5.5	1-2057769-3
2	A	4.9	1-2057769-2
2	A	4.5	1-2057769-1
3	-	5.5	2057769-6
3	-	4.9	2057769-5
3	-	4.5	2057769-4
2	-	5.5	2057769-3
2	-	4.9	2057769-2
2	-	4.5	2057769-1
FINISH	KEY POSITION	DIM M	PART NUMBER



REFER TO WWW.TE.COM  
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	03JUN2011	<b>TE</b> Connectivity
DIMENSIONS:		CHK	03JUN2011	
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	03JUN2011	NAME: IMPACT, 5 PAIR, 8 COLUMN, HEADER LEFT GUIDED, OPEN END WALL SIGNAL MODULE, 0.39 PTH SIZE: CAGE CODE DRAWING NO. RESTRICTED TO A100779C=2057769
0 PLC	±	PRODUCT SPEC		
1 PLC	±0.25	APPLICATION SPEC		
2 PLC	±0.13	WEIGHT		
3 PLC	±	CUSTOMER DRAWING		SCALE 5:1 SHEET 2 OF 2 REV A
4 PLC	±			
ANGLES	±			
FINISH	SEE TABLE			