


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
W		REVISED PER ECR-24-213591	28JUN2024	RK	FJS



- 1 PHENOLIC, BLACK.
- 2 DIALYL PHTHALATE, BLUE.
- 3 EACH POST WILL ACCEPT (SEE TABLE) TERMINATIONS OF #24 AWG MAX WIRE.
- 4 0.76um[.000030] MIN PRECIOUS METAL PLATE ON MATING END FOR A LENGTH OF 5.08[.200] MIN. GOLD FLASH ON THE REMAINDER OVER 0.76um[.000030] MIN NICKEL. CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPEC 108-10042, BASED ON EIA-364-1000.01 (CONTROLLED ENVIRONMENT APPLICATIONS).
- 5 2.54um[.000100] MIN TIN-LEAD OVER 2.54um[.000100] MIN NICKEL.
- 6 POSTS ARE SEMI-AUTOMATICALLY WIRABLE.
- 7 5.54[.218] IS REQUIRED WHEN JACKSCREWS ARE USED.
- 8 2.54um[.000100] MIN TIN OVER 2.54um[.000100] MIN NICKEL.
- 9 2.54um[.000100] MIN TIN OVER 1.27um[.000050] MIN NICKEL.
- 10 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

10	OBSOLETE	8	9	1	1	6.63 [.261]	6-205505-4
10	OBSOLETE	8	4	1	1	6.63 [.261]	6-205505-3
		8	4	1	3	16.74 [.659]	6-205505-2
	OBSOLETE	5	4	2	3	16.74 [.659]	4-205505-6
10	OBSOLETE	5	5	1	1	6.63 [.261]	3-205505-3
10	OBSOLETE	5	4	1	1	6.63 [.261]	3-205505-1
		5	4	1	3	16.74 [.659]	205505-1
	POST FINISH	CONTACT FINISH	HOUSING	NO OF TERM	A	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. OBERMAN CHK R. STONE APVD G. STEINHÄUER	13 OCT 97 30 SEP 97 31 OCT 97	TE Connectivity			
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	0. PLC 1. PLC 2. PLC 3. PLC 4. PLC ANGLES	± - ± - ± 0.13 [.005] ± - ± -	NAME	CONNECTOR ASSEMBLY, POSTED SOCKET, 34 POSITION, M SERIES		
MATERIAL SEE CALLOUT	FINISH SEE CALLOUT	WEIGHT 0.000000	A1	SIZE 00779	CAGE CODE 205505	DRAWING NO	RESTRICTED TO
CUSTOMER DRAWING				SCALE 2:1	SHEET 1 of 1	REV W	