



D

D




C

C



B

B



A

A

- 1 DOUBLE BAR POLARIZATION SLOTS.
- 2 CENTER POLARIZATION SLOT.
- 3 STANDOFFS:  
ALL POSITION SIZES-2 LOCATED AT ENDS OF HOUSING.  
20 THRU 34 POSITION SIZES-1 ADDITIONAL STANDOFF CENTERED ON HOUSING.  
40 THRU 50 POSITION SIZES- 2 ADDITIONAL STANDOFFS EVENLY SPACED WITHIN REMAINING LENGTH OF HOUSING.
- 4 NUMBER 1 POSITION INDICATOR.
- 5 DATUMS -U- AND -V- TO BE ESTABLISHED BY CUSTOMER.
- 6 HOUSING: GLASS FILLED NYLON OR PBT, BLACK, UL 94V-O RATED.  
POSTS: BRASS.
- 7 POSTS: GOLD FLASH OVER  
PALLADIUM-NICKEL PLATE, .000030 MIN TOTAL ON THE MATING SURFACES,  
.000100 MIN TIN-LEAD PLATE ON THE LOCALIZED TIN-LEAD PLATE AREA,  
.000050 MIN NICKEL UNDERPLATE ON THE ENTIRE POST.  
-OR-  
.000030 MIN GOLD PLATE ON THE MATING SURFACES,  
.000100 MIN TIN-LEAD PLATE ON THE LOCALIZED TIN-LEAD PLATE AREA,  
.000050 MIN NICKEL UNDERPLATE ON THE ENTIRE POST.
- 8 PRELIMINARY - PROPOSED DESIGN. NOT RELEASED FOR PRODUCTION

OBSOLETE	2.300	1.900	19	40	2057111-8
	2.000	1.600	16	34	2057111-7
	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. POLIGNONE 18JUN08	TE Connectivity		
DIMENSIONS: INCHES		CHK S. BOLASH 18JUN08	NAME		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APP'D S. BOLASH 18JUN08	PRODUCT SPEC		
0. PLC ± .005		APPLICATION SPEC		RESTRICTED TO	
1. PLC ± .005		SIZE		CAGE CODE	
2. PLC ± .005		DRAWING NO		REV	
3. PLC ± .005		WEIGHT		SCALE	
4. PLC ± .005		CUSTOMER DRAWING		SHEET	
ANGLES ± .005		100779		1 OF 1	
FINISH		2057111		REV	
6		7		B1	