


© 1973 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.


Unpublished copy not to be reproduced without written permission of AMP Incorporated.



REVISIONS				
ZONE	LTR	DESCRIPTION	DATE	APPROVED
	0	RELEASED WAS 5064-45 NO.	10/5/73	gms
	A	REV PER ECN 6-669	8/5/73	gms
	B	CHANGED MAT'L ECN E-779	11/28/76	gms
	L	REV PER ECN J-985	1-28-83	gms
	D	REVISED PER ECO-16-010129	03AUG16	CTT

- 206495 - 3 1. AS SHOWN.
- 2. PLATING : GOLD PER MIL-G-45204 OVER COPPER MIL-C-14550.
- 206495 - 4 1. SAME AS -3 EXCEPT:
- 2. CONTACTS ON TAPE.
- 206495-6 1. SAME AS -3

1. WIRE BARREL WILL ACCEPT # 26-28 AWG WIRE.
2. CRIMP CONTACT PER TE I.S.408-7516.
3. INSERTION/EXTRACTION TOOL TE 91067-1.
4. RESTRICTED TO SPACE SYSTEMS LORAL.
5. POINT OF PLATING THICKNESS MEASUREMENT.



WHEN ORDERING CONTACT ON TAPE, ORDER BY THE TAPE NUMBER PLUS THE PACKAGING CODE AS FOLLOWS:

1. FOR USE WITH AMP TAPETRONIC, PNEUMATIC TOOL -
 - A. 1000 PARTS TO A BOX ADD PACKAGING CODE: 1MBOX
2. FOR USE WITH 4/8 INDENT STRIPPER CRIMPER -
 - A. 1000 PARTS TO A REEL ADD PACKAGING CODE: 1MREEL
 - B. 5000 PARTS TO A REEL ADD PACKAGING CODE: 5MREEL

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON: DECIMALS ± .004 ANGLES ± .04		CONTRACT NO.		NAME	
MATERIAL		DR. <i>10/5/73</i>		AMP HARRISBURG, PENNSYLVANIA	
BERYLLIUM COPPER PER ASTM B197		APRD <i>10/12/73</i>		CONTACT, PIN SIZE 22D	
		D. <i>10-18-73</i>		SIZE CODE IDENT. NO. NUMBER	
		RE <i>10-19-73</i>		B 00779 206495	
		DSGN APPD		SCALE 10:1	
		OTHER APPD		SHEET 10F1	