






ASSEMBLY CONNECTIVITY			
FULLAXS LC		FULLAXS LC	
PIN A	↔	PIN B	
PIN B	↔	PIN A	

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-2061614-Y	XY.0

- NOTES:
- MAX. CONNECTOR ATTENUATION 0.3 dB, MEASURED AT 850 nm ACCORDING TO I.E.C. 61300-3-4 INSERTION METHOD B
 - MIN. RETURN LOSS 25 dB, IN MATED CONDITION AGAINST REFERENCE CONNECTOR AT 850 nm
 - INFORMATION ON LABEL, SEE DETAIL FOR EXAMPLE
 - BARCODE
 - UNIQUE TE SERIAL NUMBER
 - ASSEMBLY LENGTH
 - TE CONNECTIVITY PART NUMBER & ORDER NUMBER
 - CABLE INFORMATION:
 - CORE DIAMETER: 50/125 μ m (2x)
 - OUTER JACKET DIAMETER: 4.8 mm
 - OUTER JACKET COLOUR: BLACK
 - OUTER JACKET MATERIAL: HALOGEN FREE FLAME RETARDANT
 - CABLE ATTENUATION: 3.0 dB/km @ 850 nm OR 1.0 dB/km @ 1300 nm

△ LABEL DETAIL:



1	INFORMATION LABEL		4
2	FULLAXS OVERMOLDED LC DUPLEX PLUG ASSEMBLY, MM, BLACK		3
2	FULLAXS OVERMOLDED DROP PROTECTION, BLACK		2
L	FOCAB Ø4.8 mm, 2FOLD, MULTI MODE OM3, BLACK		1
Qty	Description		Item
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN R. COOLEN 09NOV2011 CHK S. BORGAS 15JAN2013 APVD A. HENGELMOLEN 15JAN2013 PRODUCT SPEC — APPLICATION SPEC 114-32032 WEIGHT 0.000000 TE TE Connectivity FIBER OPTIC LEAD 4.8 mm FULLAXS LC/DPX – FULLAXS LC/DPX MULTI MODE OM3
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:	NAME
		0 PLC ± – 1 PLC ± – 2 PLC ± – 3 PLC ± – 4 PLC ± – ANGLES ± –	
MATERIAL —			FINISH —
			CAGE CODE 00779
			DRAWING NO C=2061614
			RESTRICTED TO —
			SCALE NTS
			SHEET 1 of 1
			REV B