




- 1

HOUSING MATERIAL: PA66, BLACK, UL 94 V-0 RATED.
- 2

CONTACT MATERIAL: BRASS PER ASTM B36.
- 3

3.81µm [0.000150] MIN TIN OVER 2.54µm [0.000100] MIN COPPER.
- 4

0.76µm [0.000030] MIN PRECIOUS METAL PLATE FOR A LENGTH OF 5.08 [0.200] FROM MATING END, 3.81µm [0.000150] MIN TIN-LEAD FOR A LENGTH OF 4.83 [0.190] MIN FROM OPPOSITE END, BOTH OVER 1.27µm [0.000050] MIN NICKEL.
- 5

CONTACTS SELECT LOADED IN POSITIONS 2, 3 AND 4.
- 6

3.81µm [0.000150] MIN TIN OVER 2.54µm [0.000100] MIN COPPER.
- 7

0.76µm [0.000030] MIN PRECIOUS METAL PLATE FOR A LENGTH OF 5.08 [0.200] FROM MATING END, 3.81µm [0.000150] MIN TIN FOR A LENGTH OF 4.83 [0.190] MIN FROM OPPOSITE END, BOTH OVER 1.27µm [0.000050] MIN NICKEL.
- 8

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

8	5	OBSOLETE	6	YES	1-207119-2
		OBSOLETE	7	NO	1-207119-1
			7	YES	1-207119-0
			6	NO	207119-9
8	5	OBSOLETE	6	YES	207119-8
		OBSOLETE	3	YES	207119-7
		OBSOLETE	4	NO	207119-4
		OBSOLETE	4	YES	207119-3
		OBSOLETE	3	NO	207119-2
		OBSOLETE	3	YES	207119-1
		CONTACT FINISH	MOUNTING TABS		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.SIPE 03/10/92	TE Connectivity		
		CHK R.STONE 3-17-92			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± -		PRODUCT SPEC	
		1 PLC ± -		108-10033	
		2 PLC ± 0.25 [010]		APPLICATION SPEC	
MATERIAL		FINISH		WEIGHT	
1-2		CONTACT: SEE TABLE		A2 00779	
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 OF 1
				REV Z	