




LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE
HB	-			D1 ADD NEW PN ECO-19-017316	13-Nov-19

DWN	APVD	DWN	APVD
Huang.Yunshou	Yu.Banghua	Zhang.Sunny	

PRODUCT SPEC	APPLICATION SPEC	WEIGHT	

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=2071137	

SCALE	SHEET	REV
5:1	1 OF 2	D1



CONNECTION FIGURE




FIGURE FOR PRINTED CIRCUIT BOARD PROCESSING (BOTTOM VIEW)




Diagram dimension	Tolerance
0.99mm max.	±0.1mm
1 - 2.99mm	±0.2mm
3mm min.	±0.3mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
	ANGLES ± -
MATERIAL	FINISH
-	-

DWN	CHK	APVD	PRODUCT SPEC	APPLICATION SPEC	WEIGHT
Huang.Yunshou	Yu.Banghua	Zhang.Sunny			

TE Connectivity	NAME		OJ-SH-LMH2-WG CUSTOMER DRAWING	
	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	A3	00779	C=2071137	

CUSTOMER DRAWING	SCALE	SHEET	REV
	5:1	1 OF 2	D1

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

HB

-

SEE SHEET 1

NOTES:

1.TERMINAL DIMENSIONS BEFORE SOLDER DIP

2.LOT NO. SYSTEM AS FOLLOWING:

WEEK

YEAR

3.FOR THE TIN-PLATING OF THE PINS:

+0.1mm FOR WIDTH,THICKENSS AND DIAMETER.

+0.5mm FOR LENGTH.

4.MARKING FROM INK TO LASER.

5.ADD LOT NO. SYSTEM AS FOLLOWING;

1

1

A

II

III

I, DIGITS FOR DAY OF THE WEEK

1...MONDAY IN THIS WEEK;

2...TUESDAY IN THIS WEEK;

.....

7...SUNDAY IN THIS WEEK

II, DIGITS FOR SHIFT OF THE DAY

1...DAY SHIFT IN THIS DAY;

2...NIGHT SHIFT IN THIS DAY;

III, ONE CHARACTER DISTINGUISH THE

LINE IDENTITY, SUCH AS: A,B.....Z

107-79010

2071137-2

OJ-SH-105LMH2-WG,00000

b

107-79010

2071137-1

OJ-SH-112LMH2-WG, 00000

a

PACKING SPEC

TE PART NO

DESCRIPTION

TYPE

RELAY TYPE

		UV SEAL	SEAL (HOLE)	16
		EPOXY RESIN	SEAL (BASE & BOBBIN)	15
		3UEW	MAGNETIC WIRE	14
UL94V-0		P.B.T	CASE	13
UL94V-0		P.B.T	BASE	12
UL94V-0		P.B.T	BOBBIN	11
	SOLDER DIP	C.P WIRE	COIL TERMINAL	10
UL94V-0		P.P.S	CARD	9
		Ag ALLOY	MOVABLE CONTACT	8
		Ag ALLOY	NO.CONTACT	7
		STEEL	HINGE SPRING	6
	SOLDER DIP	Cu ALLOY	NO.TERMINAL	5
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	4
	NIP	STEEL	CORE	3
	NIP	STEEL	ARMATURE	2
	NIP	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

± -

± -

± -

± -

± -

± -

MATERIAL

-

FINISH

-

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

Huang.Yunshou

Yu.Banghua

Zhang.Sunny

-

-

-

-

TE

TE Connectivity

NAME

OJ-SH-LMH2-WG CUSTOMER DRAWING

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=2071137

-

SCALE

SHEET

REV

5:1

2 OF 2

D1

1470-19

(3/11)