



1 CONNECTOR WILL ACCEPT POSTED TYPE III+ PIN CONTACTS.

2 OBSOLETE PARTS:

3 .000030 MIN PRECIOUS METAL PLATE ON MATING END FOR A LENGTH OF .200 MIN OVER .000050 MIN NICKEL PLATE. GOLD FLASH ALL OVER. CONFORMS TO THE REQUIREMENTS OF TE CONNECTIVITY PRODUCT SPEC 108-10042, BASED ON EIA/ECA-364-1000.01A (CONTROLLED ENVIRONMENTAL APPLICATIONS.)



	OBSOLETE	NO	YES	TIN		.130	1-207303-7
		NO	YES	TIN		.119	1-207303-6
		NO	NO	TIN	TIN	.220	1-207303-5
		NO	YES	TIN		.220	1-207303-4
		NO	NO	TIN		.220	1-207303-3
		OBSOLETE	YES	NO	TIN-LEAD		.220
BY 1-207303-4		NO	YES	TIN-LEAD	GOLD	.220	1-207303-1
	OBSOLETE	NO	NO	TIN-LEAD		.220	207303-3
	OBSOLETE	NO	NO	TIN-LEAD	TIN	.220	207303-1
	PERIPHERAL SEAL	THREADED INSERTS	CONTACT POST FINISH	CONTACT BODY FINISH	A	PART NUMBER	

RECOMMENDED P.C. BOARD LAYOUT

BOTTOM NON-COMPONENT SIDE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.LEE BG 7-2-91		 TE Connectivity				
		CHK W.G.LENKER 4-14-92						
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE ASSEMBLY, POSTED, STD SEX, SERIES 1, 17-16, CPC —				
		APVD —						
		PRODUCT SPEC 108-10024						
		APPLICATION SPEC —						
				SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL SEE CALLOUT		FINISH SEE TABLE		WEIGHT —		A2 00779 C=207303		—
CUSTOMER DRAWING				SCALE 2:1		SHEET 1 OF 1		REV V.1