



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	AA	REVISED PER ECR-24-213594	01JUL2024	RK	FJS



- 1

HOUSING MATERIAL: PA66, BLACK, UL 94 V-0 RATED.
- 2

CONTACT MATERIAL: BRASS PER ASTM B36.
- 3

3.81µm [.000150] MIN TIN OVER 2.54µm [.000100] MIN COPPER.
- 4

0.76µm [.000030] MIN PRECIOUS METAL PLATE FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81µm [.000150] MIN TIN FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- 5

.000150 MIN TIN OVER .000100 MIN CU, OR .000050 MIN NICKEL.
- 6

0.76µm [.000030] MIN PRECIOUS METAL PLATE FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81µm [.000150] MIN TIN FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.

OBSOLETE	6	NO	1-207158-1
	6	YES	1-207158-0
	5	NO	207158-8
	5	YES	207158-7
OBSOLETE	4	NO	207158-4
	4	YES	207158-3
OBSOLETE	3	NO	207158-2
	3	YES	-207158-1
CONTACT FINISH		MOUNTING TABS	PART NO
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 03/10/92 L.SIPE CHK 3-17-92 R.STONE APVD 3-17-92 A.TRAVIS PRODUCT SPEC 108-10033 APPLICATION SPEC — WEIGHT — CUSTOMER DRAWING	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.25 [.010] 3 PLC ± — 4 PLC ± — ANGLES ± — FINISH CONTACT: SEE TABLE	
MATERIAL 1-2		NAME PIN HEADER ASSEMBLY, 6 POSITION, METRIMATE	
		SIZE A2	CAGE CODE 00779
		DRAWING NO C-207158	RESTRICTED TO —
		SCALE 4:1	SHEET 1 OF 1
		REV AA	