







RECOMMENDED PC BOARD LAYOUT



- 1
- HOUSING MATERIAL: PA66, BLACK, UL 94 V-0 RATED
- 2
- BRASS PER ASTM B36.
- 3
- 3.81µm [.000150] MIN TIN-LEAD OVER 2.54µm [.000100] MIN COPPER OR 1.27µm [.000050] MIN NICKEL.
- 4
- 0.76µm [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] MIN FROM MATING END 3.81µm [.000150] MIN TIN-LEAD FOR A LENGTH OF 5.36 [.211] MIN FROM OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- 5
- .000150 MIN TIN OVER .000100 MIN CU, OR .000050 MIN NICKEL.
- 6
- 0.76µm [.000030] MIN PRECIOUS METAL PLATE FOR A LENGTH OF 5.08 [.200] MIN FROM MATING END 3.81µm [.000150] MIN TIN FOR A LENGTH OF 5.36 [.211] MIN FROM OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- 7
- PRELIMINARY PART NUMBER.
- 8
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.

8	OBSOLETE	3.50 [.137]	6	1-207365-0
	OBSOLETE	7.52 [.296]	6	-207365-9-
		4.72 [.186]	6	207365-8
		4.72 [.186]	5	207365-7
	OBSOLETE	7.52 [.296]	4	-207365-6-
	OBSOLETE	4.72 [.186]	4	207365-3
	OBSOLETE	4.72 [.186]	3	207365-1
		A	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
HOUSING: 1
CONTACTS: 2

FINISH
CONTACTS: SEE TABLE

DWN L.SIPE 07/20/92
CHK R.STONE 7-24-92
APVD A.TRAVIS 7-24-92

PRODUCT SPEC
APPLICATION SPEC
WEIGHT -

CUSTOMER DRAWING

TE Connectivity

PIN HEADER ASSEMBLY, 3 POSN,
IN-LINE, SMALL METRIC CONNECTOR,
METRIMATE

SIZE A2 CAGE CODE 00779 DRAWING NO C-207365

RESTRICTED TO -

SCALE 2:1 SHEET 1 OF 1 REV S