




- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 1 HOUSING MATERIAL: PA66, BLACK, UL 94 V-0 RATED.
- 2 CONTACT MATERIAL: PHOSPHOR BRONZE.
- 3.81 μ m [.000150] MIN TIN-LEAD OVER 1.27 μ m [.000050] MIN NICKEL.
- 0.76 μ m [.000030] MIN GOLD FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END, 3.81 μ m [.000150] MIN TIN-LEAD FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27 μ m [.000050] MIN NICKEL.
- 3.81 μ m [.000150] MIN TIN OVER 1.27 μ m [.000050] MIN NICKEL.
- 0.76 μ m [.000030] MIN PRECIOUS METAL PLATE FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END, 3.81 μ m [.000150] MIN TIN FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27 μ m [.000050] MIN NICKEL.
- OBSELETE PARTS: OBSELETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	6	NO	1-207524-0
	6	YES	207524-9
7 OBSELETE	5	NO	-207524-8-
	5	YES	207524-7
	4	NO	207524-4
OBSELETE	4	YES	-207524-3-
OBSELETE	3	NO	207524-2
OBSELETE	3	YES	207524-1
CONTACT FINISH		MOUNTING TABS	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	03/20/92	TE TE Connectivity	
		L.SIPE	3-25-92		
		CHK	R.STONE	NAME	
		APVD	A.TRAVIS		
		PRODUCT SPEC	108-10033	APPLICATION SPEC	
		FINISH	-		
MATERIAL		WEIGHT	-	SIZE	CAGE CODE
SEE NOTE		CONTACT: SEE TABLE	-	A2	00779
				DRAWING NO	RESTRICTED TO
				C=207524	-
				SCALE	SHEET
				4:1	1 OF 1
				REV	Z
				CUSTOMER DRAWING	