





REVISIONS					
P	LTR	DESCRIPTION	DATE	OWN	APVD
	N	REVISED PER ECR-24-213594	01JUL2024	RK	FJS




RECOMMENDED PC BOARD LAYOUT



- 1 HOUSING MATERIAL: PA66, BLACK, UL 94 V-0 RATED
- 2 BRASS PER ASTM B36.
- 3 3.81µm [.000150] MIN TIN-LEAD OVER 2.54µm [.000100] MIN COPPER OR 1.27µm [.000050] MIN NICKEL.
- 4 0.76µm [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] MIN FROM MATING END, 3.81µm [.000150] MIN TIN-LEAD FOR A LENGTH OF 5.51 [.217] MIN FROM OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- 5 .000150 MIN TIN OVER .000100 MIN CU, OR .000050 MIN TIN.
- 6 0.76µm [.000030] MIN PRECIOUS METAL PLATE FOR A LENGTH OF 5.08 [.200] MIN FROM MATING END, 3.81µm [.000150] MIN TIN FOR A LENGTH OF 5.51 [.217] MIN FROM OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.

	6	207378-7
	5	207378-6
OBSOLETE	4	207378-3
OBSOLETE	3	207378-1
FINISH		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN L.SIPE 07/07/92	 TE Connectivity					
			CHK R.STONE 7-24-92						
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [0.10] 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD A.TRAVIS 7-24-92	NAME					
			PRODUCT SPEC —	PIN HEADER ASSY, 6 POSN, IN-LINE, RIGHT ANGLE, SMALL METRIC CONNECTOR, METRIMATE					
			APPLICATION SPEC —						
			—						
			—						
MATERIAL	FINISH	WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C-207378	RESTRICTED TO —			
HOUSING: 		CONTACTS: SEE TBL		CUSTOMER DRAWING			SCALE 2:1	SHEET 1 OF 1	REV N