




REVISIONS					
P	LTR	DESCRIPTION	DATE	DMN	APVD
S		REVISED PER ECO-18-000437	18JAN2020	RS	MZ
T		REVISED PER ECO-20-002046	17FEB2020	RK	MZ



- 1 HOUSING MATERIAL: PA66, BLACK, UL 94 V-0 RATED.
- 2 CONTACT MATERIAL: PHOSPHOR BRONZE.
- 3 $3.81\mu\text{m}$ [.000150] MIN TIN-LEAD OVER $1.27\mu\text{m}$ [.000050] MIN NICKEL.
- 4 $0.76\mu\text{m}$ [.000030] MIN GOLD FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END $3.81\mu\text{m}$ [.000150] MIN TIN-LEAD FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER $1.27\mu\text{m}$ [.000050] MIN NICKEL.
- 5 $3.81\mu\text{m}$ [.000150] MIN TIN OVER $1.27\mu\text{m}$ [.000050] MIN NICKEL.
- 6 $0.76\mu\text{m}$ [.000030] MIN GOLD FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END $3.81\mu\text{m}$ [.000150] MIN TIN FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER $1.27\mu\text{m}$ [.000050] MIN NICKEL.

OBSOLETE	4.60	[.181]	$\Delta 6$	NO	4-207532-1-
	4.60	[.181]	$\Delta 6$	YES	1-207532-0
	4.60	[.181]	$\Delta 5$	NO	207532-9
	4.60	[.181]	$\Delta 5$	YES	207532-8
OBSOLETE	9.68	[.381]	$\Delta 3$	NO	-207532-7-
OBSOLETE	4.60	[.181]	$\Delta 4$	NO	207532-4
OBSOLETE	4.60	[.181]	$\Delta 4$	YES	207532-3
OBSOLETE	4.60	[.181]	$\Delta 3$	NO	207532-2
OBSOLETE	4.60	[.181]	$\Delta 3$	YES	207532-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN L-SIZE 03/19/92	APVD R. STONE 3-25-92	NAME
0 PLC ± -	1 PLC ± -	2 PLC ± 0.25 [.010]	3 PLC ± -	4 PLC ± -
ANGLES ± -				
MATERIAL SEE NOTES	FINISH CONTACT: SEE TABLE	WEIGHT	SIZE A1	CAGE CODE 00779
			DRAWING NO. 207532	RESTRICTED TO
			CUSTOMER DRAWING	SCALE 4:1 SHEET 1 OF 1 REV T

STE TE Connectivity

SOCKET HEADER ASSEMBLY, 24 POSITION, METRIMATE

108-10033