





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - L1 ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
M		REVISED PER ECO-18-000443	18JAN2018	RS	MZ
N		REVISED PER ECO-20-001562	04FEB2020	SG	MZ



- ① HOUSING MATERIAL: PA66, BLACK, UL 94 V-0 RATED
- ② BRASS PER ASTM B36.
- ③ $3.81\mu\text{m}$ [$.000150$] MIN TIN-LEAD OVER $2.54\mu\text{m}$ [$.000100$] MIN COPPER OR $1.27\mu\text{m}$ [$.000050$] MIN NICKEL.
- ④ $0.76\mu\text{m}$ [$.000030$] MIN GOLD FOR A LENGTH OF 5.08 [$.200$] MIN FROM MATING END, $3.81\mu\text{m}$ [$.000150$] MIN TIN-LEAD FOR A LENGTH OF 5.36 [$.211$] MIN FROM OPPOSITE END, BOTH OVER $1.27\mu\text{m}$ [$.000050$] MIN NICKEL.
- ⑤ $.000150$ MIN LEAD FREE TIN OVER $.000100$ MIN COPPER, OR $.000050$ MIN NICKEL.
- ⑥ $0.76\mu\text{m}$ [$.000030$] MIN GOLD FOR A LENGTH OF 5.08 [$.200$] MIN FROM MATING END, $3.81\mu\text{m}$ [$.000150$] MIN TIN FOR A LENGTH OF 5.36 [$.211$] MIN FROM OPPOSITE END, BOTH OVER $1.27\mu\text{m}$ [$.000050$] MIN NICKEL.

FINISH	PART NO
⑥	207398-7
⑤	207398-6
④	207398-3
③	207398-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	L.SIPE	07/07/92	 TE Connectivity Ltd.
DIMENSIONS: mm [INCHES]		CHK	R.STONE	7-24-92	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	A.TRAVIS	7-24-92	
0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC	NAME		
MATERIAL	HOUSING: ① CONTACTS: ②	FINISH	CONTACTS: SEE TABLE		PIN HDR ASSY, 10 POSN, IN-LINE, RIGHT ANGLE, SMALL METRIC CONNECTOR, METRIMATE
WEIGHT	-	SCALE	A2	00779	SIZE CAGE CODE DRAWING NO RESTRICTED TO C=207398
CUSTOMER DRAWING		SCALE	2:1	SHEET	1 of 1
		REV	N		