

- SEE SHEET 2 FOR WIRING SCHEMATIC.
- PRODUCT AND PROCESSING MUST MEET THE REQUIREMENTS OF TE TEC-138-702.
- CHARACTERISTIC IMPEDANCE: 100±10Ω (MEASURED DIFFERENTIALLY)
- CABLE ASSEMBLY TO BE TESTED FOR OPENS, SHORTS AND PROPER EEPROM PROGRAM.
- EEPROM DOES NOT INCLUDE PAGE SWAPPING.
- THIS P/N HAS BEEN OPTIMIZED FOR USE AT 5 GBPS (DDR).


△	-	-	EQUALIZED	28	6.0±0.1	2074119-9
△	-	-	EQUALIZED	28	5.0±0.1	2074119-8
△	-	-	EQUALIZED	28	5.0±0.1	2074119-7
△	-	-	EQUALIZED	28	4.0±0.1	2074119-6
△	-	-	EQUALIZED	30	4.0±0.1	2074119-5
△	-	-	EQUALIZED	30	3.0±0.1	2074119-4
△	-	-	EQUALIZED	30	2.0±0.1	2074119-3
△	-	-	UNEQUALIZED	30	1.0±0.1	2074119-2
△	-	-	UNEQUALIZED	30	0.5±0.1	2074119-1
	CUSTOMER EC	CUSTOMER P/N		AWG	L METERS	TYCO ELECTRONICS P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN 200CT2008	APVD	NAME
0 PLC ± -	1 PLC ± -	250CT2008	J. ELLISON	CABLE ASSEMBLY, DIRECT ATTACH QSFP TO 4X
2 PLC ± -	3 PLC ± -		J. ELLISON	
4 PLC ± -	ANGLES ± -			
MATERIAL	FINISH	WEIGHT	SIZE	CAGE CODE
			A1	00779
			DRAWING NO	DRAWING NO
			2074119	2074119
			RESTRICTED TO	RESTRICTED TO
			CUSTOMER DRAWING	CUSTOMER DRAWING

STE TE Connectivity

SCALE: N.T.S. SHEET 1 OF 2 REV G



WIRING PATTERN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.DU 200CT2008		
		CHK J.JELLISON 25OCT2008		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CABLE ASSEMBLY, DIRECT ATTACH QSFP TO 4X
		0. PLC ± -	1. PLC ± -	PRODUCT SPEC
		2. PLC ± -	3. PLC ± -	APPLICATION SPEC
		4. PLC ± -	ANGLES ± -	RESTRICTED TO
MATERIAL	FINISH	WEIGHT	SIZE A1	CAGE CODE 00779
			DRAWING NO. 2074119	SCALE N.T.S.
CUSTOMER DRAWING		SHEET 2 OF 2		REV G