





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
P		REVISED PER ECR-24-213594	01JUL2024	RK	FJS



RECOMMENDED PC BOARD LAYOUT



- 1 HOUSING MATERIAL: PA66, BLACK, UL94 V-0 RATED
- 2 BRASS PER ASTM B36.
- 3 $3.81\mu\text{m}$ [.000150] MIN TIN-LEAD OVER $2.54\mu\text{m}$ [.000100] MIN COPPER OR $1.27\mu\text{m}$ [.000050] MIN NICKEL.
- 4 $0.76\mu\text{m}$ [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] MIN FROM MATING END, $3.81\mu\text{m}$ [.000150] MIN TIN-LEAD FOR A LENGTH OF 5.36 [.211] MIN FROM OPPOSITE END, BOTH OVER $1.27\mu\text{m}$ [.000050] MIN NICKEL.
- 5 $3.81\mu\text{m}$ [.000150] MIN TIN OVER $2.54\mu\text{m}$ [.000100] MIN COPPER OR $1.27\mu\text{m}$ [.000050] MIN NICKEL.
- 6 $0.76\mu\text{m}$ [.000030] MIN PRECIOUS METAL PLATE FOR A LENGTH OF 5.08 [.200] A LENGTH MIN FROM MATING END, $3.81\mu\text{m}$ [.000150] MIN TIN FOR $1.27\mu\text{m}$ OF 5.36 [.211] MIN FROM OPPOSITE END, BOTH OVER [.000050] MIN NICKEL.
- 7 PRILIMINARY PART NUMBER.
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

8	OBSOLETE	3.50 [.137]	6	1-207584-0
	OBSOLETE	7.52 [.296]	6	207584-9
8	OBSOLETE	4.72 [.186]	6	207584-8
		4.72 [.186]	5	207584-7
8	OBSOLETE	7.52 [.296]	4	207584-6
	OBSOLETE	4.72 [.186]	4	207584-3
8	OBSOLETE	4.72 [.186]	3	207584-1
		A	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.SIPE 07/21/92	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK R.STONE 7-24-92		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD -	NAME	
		PRODUCT SPEC -		
	FINISH CONTACTS: SEE TABLE	APPLICATION SPEC -	SIZE CAGE CODE DRAWING NO	
		WEIGHT -		
MATERIAL HOUSING: 1	CONTACTS: 2	CUSTOMER DRAWING	A2 00779 C=207584	RESTRICTED TO -
SCALE 2:1			SHEET 1 OF 1	REV P