





207526

- | | | | |
|----------|---|---------------|---------------------|
| |  | NO | 1-207526-0 |
| |  | YES | 207526-9 |
| |  | NO | 207526-8 |
| |  | YES | 207526-7 |
| OBSOLETE |  | NO | 207526-4 |
| OBSOLETE |  | YES | 207526-3 |
| OBSOLETE |  | NO | 207526-2 |
| OBSOLETE |  | YES | 207526-1 |
| | CONTACT FINISH | MOUNTING TABS | PART NO |

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 03/20/92 L.SIPE CHK 3--25--92 R.STONE		 TE Connectivity			
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME SOCKET HEADER ASSEMBLY, 9 POSITION, METRIMATE			
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± ±					
MATERIAL SEE NOTE		FINISH CONTACT: SEE TABLE					
		APVD - PRODUCT SPEC 108-10033 APPLICATION SPEC -		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT -		A2	00779	C-207526	-
CUSTOMER DRAWING						SCALE	4:1
						SHEET	1 of 1
						REV	T