




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
U		REVISED PER ECR-24-213594	01JUL2024	RK	FJS



RECOMMENDED LAYOUT

- 1 HOUSING MATERIAL: PA66, BLACK, UL 94 V-0 RATED.
- 2 CONTACT MATERIAL: PHOSPHOR BRONZE.
- 3 3.81µm [.000150] MIN TIN-LEAD OVER 1.27µm [.000050] MIN NICKEL.
- 4 0.76µm [.000030] MIN GOLD FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END 3.81µm [.000150] MIN TIN-LEAD FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- 5 3.81µm [.000150] MIN TIN OVER 1.27µm [.000050] MIN NICKEL.
- 6 0.76µm [.000030] MIN PRECIOUS METAL PLATE FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END 3.81µm [.000150] MIN TIN FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.

OBSOLETE	4.60	[.181]	6	NO	4-207532-1-
	4.60	[.181]	6	YES	1-207532-0
	4.60	[.181]	5	NO	207532-9
	4.60	[.181]	5	YES	207532-8
OBSOLETE	9.68	[.381]	3	NO	-207532-7-
OBSOLETE	4.60	[.181]	4	NO	207532-4
OBSOLETE	4.60	[.181]	4	YES	207532-3
OBSOLETE	4.60	[.181]	3	NO	207532-2
OBSOLETE	4.60	[.181]	3	YES	207532-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. SIPE 03/19/92	TE Connectivity	
		CHK R. STONE 3-25-92		
DIMENSIONS: mm (INCHES)	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD A. TRAVIS 3-25-92	NAME	
	0 PLC ± -	PRODUCT SPEC	SOCKET HEADER ASSEMBLY, 24 POSITION, METRIMATE	
	1 PLC ± -	APPLICATION SPEC	108-10033	
	2 PLC ± 0.25 [.010]		-	
MATERIAL SEE NOTES	FINISH CONTACT: SEE TABLE	WEIGHT -	SIZE A1	CAGE CODE 00779
		SCALE 4:1	SHEET 1 OF 1	REV U