

NOTES:

D

С

В

А

1 PACK IN ACCORDANCE WITH TE SPEC 107-3275


4

TE Connectivity. All Rights Reserved.

- 2 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED
- GOLD PLATING 0.254um MIN OVER NIKEL PLATING 1.27um MIN OVER COPPER PLATING 1.27um MIN
- GOLD PLATING 0.762um MIN OVER NIKEL PLATING 1.27um MIN OVER COPPER PLATING 1.27um MIN


ELECTRICAL	MECHANICAL	ENVIRONMENTAL
Impedance (Ohm) <u>50</u>	Interface Dimension MIL—STD—348B Fig. <u>310—2</u>	TEMPERATURE RANGE 65℃ TO + 165℃
Frequency Range (GHz) <u>DC to 27GHz</u>	Recommended Coupling Torque	THERMAL SHOCK
Voltage Rating (Peak) _@ Sea Level _335_V_RMS	$_{-7 \text{ to } 10 \text{ ln}-\text{Lbs}}$	MIL-STD-202, METH.107, COND.B CORROSION
Insulation Resistance (MIN.) _ <u>5000 M ohms</u>	Force to Engage and Disengage (In/Ibs) _ <u>2.0 MAX</u>	MIL_STD_202, METH.101, COND.B
Contact Resistance (Milliohms MAX) Center Contact <u>3.0</u> Outer Contact <u>2.0</u>	Center Cantact Captivation Axial (Lbs) <u>6.0</u> Radial (In/Oz) <u>N/A</u>	VIBRATION <u>MIL-STD-202, METH.204, COND.D</u> SHOCK
Dielectric Withstand Voltage: 750 V RMS Max	Cable Retention Axial (Lbs) <u>N/A</u>	<u>MIL-STD-202, METH.213, COND.I</u> MOISTURE RESISTANCE
Insertion Loss : 0.1*SQRT(F)_dB	Mating cycles	MIL-STD-202, METH.106,
VSWR: <u>1.3 MAX (DC-27GHz)</u>		ROHS
RF leakage:N/A		COMPLIANT
3rd Intermodulation: <u>N/A</u>		

1471-9 (1/15)




1471-9 (1/15)

Α




3.A. As shown in the figure below, solder cable inner conductor with the center pin, but please leave 0.3mm gap between cable inner conductor and center pin.

B.Control the welding time and temperature, and remove the excess with tools spill the tin spots, make sure the center needle surface is smooth, then clean the welding area of excess residue.excess residue in welding area.



4.A. Insert the cable into the main body until it reaches the end face of the insulator on the cable contact with the insulator step inside the main body and cannot be pushed until.

B.As shown in the left figure, screw the sleeve into the main body and tighten it.clean the welding area of excess residue.excess residue in welding area.



[THIS DRAWING IS A CO	dwn ED	29DEC2020		_				
	DIMENCIONO		снк RZ	29DEC2020			ETE TE Co	nnectivity	
	DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	29DEC2020	NAME				
	mm		WH			EP-SMA,JACK,STRAIGHT,27GHz,			
	<u> </u>	0 PLC ± - 1 PLC ± 0.3	PRODUCT SPEC				DLDER,MATCH WITH 14		
	$\bigoplus \square$	2 PLC ± 0.2 3 PLC ± 0.1	APPLICATION SPE	0			_		
		4 PLC $\pm -$ ANGLES $\pm 5^{\circ}$	_		SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO
	MATERIAL SEE TABLE	FINISH	WEIGHT	_	A2	00779	C- 2081887		
	SEE TABLE	_	CUSTOMER	DRAWING			SCALE 10:1 SHE	2 OF 2	2 ^{REV} A

В