




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
T		REVISED PER ECR-24-213594	01JUL2024	RK	FJS

D

C

B

A



RECOMMENDED LAYOUT

- HOUSING MATERIAL: PA66, BLACK, UL 94 V-0 RATED.
- CONTACT MATERIAL: PHOSPHOR BRONZE.
- 3.81 μm [.000150] MIN TIN-LEAD OVER 1.27 μm [.000050] MIN NICKEL.
- 0.76 μm [.000030] MIN GOLD FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END 3.81 μm [.000150] MIN TIN-LEAD FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27 μm [.000050] MIN NICKEL.
- .000150 MIN LEAD FREE TIN OVER .000050 MIN NICKEL.
- 0.76 μm [.000030] MIN PRECIOUS METAL PLATE FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END 3.81 μm [.000150] MIN TIN FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27 μm [.000050] MIN NICKEL.
- PRILIMINARY PART NUMBER.
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.

OBSOLETE OBSOLETE OBSOLETE OBSOLETE OBSOLETE OBSOLETE OBSOLETE OBSOLETE	3.50 [.137]	6	YES	1-207534-2
		6	NO	-1-207534-1
		6	YES	1-207534-0
		5	NO	-207534-9
		5	YES	207534-8
		4	NO	-207534-4
		4	YES	207534-3
		3	NO	-207534-2
OBSOLETE OBSOLETE	4.60 [.181]	3	YES	207534-1
		3	YES	207534-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.SIPE CHK R.STONE APVD A. TRAVIS	03/20/92 3-25-92 3-25-92	 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
	0 PLC ± -	PRODUCT SPEC		SOCKET HEADER ASSEMBLY, 36 POSITION, METRIMATE	
	1 PLC ± -	108-10033		-	
	2 PLC ± 0.25 [.010]	APPLICATION SPEC		RESTRICTED TO	
	3 PLC ± -			SIZE CAGE CODE DRAWING NO	
MATERIAL		FINISH		A1 00779  207534	
SEE NOTE		CONTACT: SEE TABLE		SCALE 4:1 SHEET 1 OF 1 REV T	
		CUSTOMER DRAWING			