


D

С

В




## NOTES:

- 1 PACK IN ACCORDANCE WITH TE SPEC 107-3275
- 2 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED
- GOLD PLATING 0.254um MIN OVER NIKEL PLATING 1.27um MIN OVER COPPER PLATING 1.27um MIN
- GOLD PLATING 0.762um MIN OVER NIKEL PLATING 1.27um MIN OVER COPPER PLATING 1.27um MIN

ELECTRICAL	MECHANICAL	ENVIRONMENTAL		
 Impedance (Ohm) <u>50</u>	Interface Dimension MIL—STD—348B Fig. <u>310—2</u>	TEMPERATURE RANGE 65℃ TO + 165℃		
Frequency Range(GHz) <u>DC to 27GHz</u>	Recommended Coupling Torque	THERMAL SHOCK		
Voltage Rating (Peak) _@ Sea Level 335 V RMS	$\frac{7 \text{ to } 10 \text{ ln} - \text{Lbs}}{(1 - 1) \text{ ln} - \text{Lbs}}$	<u>MIL-STD-202, METH.107, COND.B</u> CORROSION		
Insulation Resistance (MIN.) _5000 M ohms	Force to Engage and Disengage (In/Ibs) _ <u>2.0 MAX</u>	MIL_STD_202, METH.101, COND.B		
Contact Resistance (Milliohms MAX) Center Contact <u>3.0</u> Outer Contact <u>2.0</u>	Center Cantact Captivation Axial (Lbs) <u>6.0</u> Radial (In/Oz) <u>N/A</u>	VIBRATION <u>MIL-STD-202, METH.204, COND.D</u> SHOCK		
Dielectric Withstand Voltage: 750 V RMS Max Insertion Loss :	Cable Retention Axial (Lbs) <u>N/A</u>	MIL-STD-202, METH.213, COND.I MOISTURE RESISTANCE		
<u> </u>	Mating cycles	<u>MIL-STD-202, METH.106,</u>		
		ROHS		
RF leakage: <u>N/A</u>		COMPLIANT		
3rd Intermodulation: N/A				



1471-9 (1/15)



1471-9 (1/15)

Α


REVISIONS

DESCRIPTION

SEE SHEET 1


3.A. As shown in the figure below, first attach the insulator to the outer shield and put it on on the center conductor of the cable, and then attach the center pin to the insulator, weld to the center conductor of the cable.

B.Control the welding time and temperature, and remove the excess with tools spill the tin spots, make sure the center needle surface is smooth, then clean the welding area of excess residue.excess residue in welding area.



4.A. Insert the cable into the main body until it reaches the end face of the insulator on the cable contact with the insulator step inside the main body and cannot be pushed until.

B.As shown in the below figure, screw the sleeve into the main body and tighten it.clean the welding area of excess residue.excess residue in welding area.



THIS DRAWING IS A CO	ONTROLLED DOCUMENT.	DWN ED CHK	29DEC2020 29DEC2020		<b>≤</b> TE	TE	Connectivit	y
DIMENSIONS: TOLERANCES UNLESS		RZ						
mm	OTHERWISE SPECIFIED:	apvd WH	29DEC2020	NAME	FP_SMA	IACK STRAIG	ант 270н <del>-</del>	
	0 PLC $\pm$ - 1 PLC $\pm$ 0.3 2 PLC $\pm$ 0.2 3 PLC $\pm$ 0.1	PRODUCT SPEC			EP-SMA,JACK,STRAIGHT,27GHz, SOLDER, MATCH WITH 086 CABLE			
+ -	4 PLC $\pm -$ ANGLES $\pm 5^{\circ}$	_		SIZE	CAGE CODE DRAWING NO			RESTRICTED
MATERIAL SEE TABLE	FINISH	WEIGHT ()		A2	00779 <b>C-</b> 20	81885		_
SEE TADLE	_	CUSTOMER DR	RAWING			scale 10:1	SHEET 2 0	F 2 REV A