

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -


ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		D	ECO-14-008835	26JUN14	AP	DM

NOTE:

1. PACKAGING ACC. TO TE SPEC.107-18032
BUNDLE EVERY 25 ASSEMBLIES WITH A RUBBER BAND
2. ELECTRICAL TEST CONTAINING "SHORT CIRCUIT TEST, CONTINUITY AND ACCURATE CAVITY ASSIGNMENT TEST" ACC. TO TE-SPEC.108-18857, SUBSECTION 3.1.1
3. ASSEMBLY COLOR: WHITE
4. KEYING: HV-4

PN	L	TOLERANCES/mm
X-2083072-1	610mm (2ft)	+/- 5
X-2083072-2	1270mm (4ft)	+/- 15
X-2083072-3	1880mm (6ft)	+/- 20
X-2083072-4	2490mm (8ft)	+/- 20
X-2083072-5	3100mm (10ft)	+/- 30
X-2083072-6	3660mm (12ft)	+/- 30
X-2083072-7	4270mm (14ft)	+/- 50
X-2083072-8	4880mm (16ft)	+/- 50



UOM	QTY	DESCRIPTION	POS.
mm	AR	Cable SVT 2xAWG18 UL WH	6
PC	1	PLUG MINI HVL HV-4	5
PC	2	MICRO QUADLOK SYSTEM SOCKET CONTACT	4
PC	2	TUBE FOR SVT CABLE	3
PC	2	MICRO QUADLOK SYSTEM PIN CONTACT	2
PC	1	OUTLET, MINI HVL 7.5mm HV-4	1
	1--X		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAVINDRA K 28MAR11	STE TE Connectivity	
DIMENSIONS: mm		CHK R.HOSSAINI 31MAR11		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R.HOSSAINI 31MAR11	NAME CABLE ASSEMBLY NECTOR S LINE 2POS. HV-4, MALE TO FEMALE	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC -	APPLICATION SPEC -	
MATERIAL -	FINISH -	WEIGHT -	SIZE A3	CAGE CODE 00779
CUSTOMER DRAWING			DRAWING NO C-2083072	RESTRICTED TO -
SCALE NTS			SHEET 1 OF 1	REV D