


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	ECR-20-004655	06OCT20	RK	SBH

NOTE:

1. PACKAGING ACC. TO TE SPEC.107-18032
BUNDLE EVERY 25 ASSEMBLIES WITH A RUBBER BAND
2. ELECTRICAL TEST CONTAINING "SHORT CIRCUIT TEST, CONTINUITY AND ACCURATE CAVITY ASSIGNMENT TEST" ACC. TO TE-SPEC.108-18857, SUBSECTION 3.1.1
3. ASSEMBLY COLOR: WHITE
4. KEYING: HV-4

	PN	L	TOLERANCES/mm
OBSOLETE	X-2083076-1	610mm (2ft)	+/- 5
	X-2083076-2	1270mm (4ft)	+/- 15
	X-2083076-3	1880mm (6ft)	+/- 20
OBSOLETE	X-2083076-4	2490mm (8ft)	+/- 20
	X-2083076-5	3100mm (10ft)	+/- 30
	X-2083076-6	3660mm (12ft)	+/- 30
	X-2083076-7	4270mm (14ft)	+/- 50
	X-2083076-8	4880mm (16ft)	+/- 50



UOM	QTY	DESCRIPTION	POS.
mm	AR	Cable SVT 2xAWG18 UL WH	4
PC	1	TUBE FOR SVT CABLE	3
PC	2	MICRO QUADLOK SYSTEM PIN CONTACT	2
PC	1	OUTLET, MINI HVL 7.5mm HV-4	1
	1--X		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 02APR11 SATHISH KUMAR.G	STE TE Connectivity	
DIMENSIONS: mm		CHK 04APR11 R.HOSSAINI		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 04APR11 R.HOSSAINI	NAME CABLE ASSEMBLY NECTOR S LINE 2POS. HV-4	
0 PLC ± -		PRODUCT SPEC	-	
1 PLC ± -		APPLICATION SPEC	-	
2 PLC ± -		WEIGHT	-	
3 PLC ± -		SIZE	CAGE CODE	DRAWING NO
4 PLC ± -			A3	00779
ANGLES ± -			C=	2083076
MATERIAL		FINISH	RESTRICTED TO	
-		-	-	
CUSTOMER DRAWING			SCALE	SHEET
			NTS	1 OF 1
			REV	D1