




SEE NOTE 1	2101143-2	2101143-3
-----	FLUROSILICONE, MIL-G-83528, TYPE C	2101143-2
-----	SILICONE RUBBER, MIL-G-83528, TYPE A	2101143-1
COMMENTS	MATERIAL	PART NO.

1. PARTS REQUIRE A STABILIZATION BAKE, 24 HOURS @125°C,
PER MIL-STD-883, METH. 1008, COND. B

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009		DWN S T Morley 02FEB2010	 TE Connectivity					
DIMENSIONS: [INCHES[mm]]		CHK S T Morley 02FEB2010						
		APVD S T Morley 02FEB2010	NAME GASKET, D-RING, RFI/EMI					
		PRODUCT SPEC -					-	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0 2 PLC ±0.01 3 PLC ±0.003 4 PLC ±0.0005 ANGLES ±- FINISH		APPLICATION SPEC -	SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
		WEIGHT -	A200779		C=2101143		-	
MATERIAL SEE TABLE		Customer Drawing			SCALE 20:1	SHEET 1	OF 1	REV B