

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 2011 BY -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REV PER ECO 12-013251	7-18-12	CT	DM
-	-	-	-	-	-
-	-	-	-	-	-
-	-	-	-	-	-

11/16-24 UNEF-2B THREAD

INSERTS: QTY 1 EACH
MATERIAL: THERMOPLASTIC,
COLOR: BLACK

INTERFACIAL SEAL: QTY 1
MATERIAL:
FLUROSILICONE RUBBER
COLOR: BLUE

SNAP RING: QTY 1
MATERIAL: STAINLESS STEEL

5/8"MODIFIED ACME
TRIPLE START THREAD

WIRE SEAL: QTY 1
MATERIAL:
FLUROSILICONE RUBBER
COLOR: BLUE

RED FULL MATE INDICATOR

TRIPLE KEYED

Ø .689

R

S

RECEPTICLE: QTY 1
MATERIAL: ALUMINUM
FINISH: SEE TABLE

.670


Ø .585

1.350

"TE" AND DATE
CODE ON 1 OF 4
FLATS

SEE DETAIL A

Ø .938




DETAIL A
SCALE 4:1

NOTES:

- 1, -3 AND -5 ARE ELECTROLESS NICKEL PLATE PER MIL-C-26074.
- 2, -4 AND -6 ARE BLACK ZINC NICKEL PERAMS-2417.

KEY OPTION	KEY ROTATION	
	"R"	"S"
NORMAL	150°	210°
A	140°	215°
B	132°	248°



B	BLACK ZINC NICKLE PLATE	21023254-6
B	NICKLE PLATE	21023254-5
A	BLACK ZINC NICKLE PLATE	21023254-4
A	NICKLE PLATE	21023254-3
NORMAL	BLACK ZINC NICKLE PLATE	21023254-2
NORMAL	NICKLE PLATE	21023254-1
KEYING OPTION	FINISH	PART NUMBER

Ø .698±.005

.669±.002

MAX. PANEL THICKNESS 1/8"

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 16MAY2011

CHK MCKIBBEN, JOHN


16MAY2011

APVD DOWHOWER, KENNETH

16MAY2011

DIMENSIONS:

INCH



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±.1
1 PLC ±.1
2 PLC ±.02
3 PLC ±.005
4 PLC ±.0005
ANGLES ±.

MATERIAL

FINISH

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

RECEPTACLE ASSEMBLY SIZE 8

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2102354

SCALE 2:1

SHEET 1 OF 1

REV B