





| LOC |   | DIST |     | REVISIONS                  |  |  |           |     |      |  |
|-----|---|------|-----|----------------------------|--|--|-----------|-----|------|--|
| -   | - | P    | LTR | DESCRIPTION                |  |  | DATE      | DWN | APVD |  |
|     |   | B    |     | RELEASED PER ECO-13-004502 |  |  | 12MAR2013 | KM  | DH   |  |
|     |   | C    |     | REVISED PER ECO-13-008265  |  |  | 20MAY2013 | DB  | DH   |  |
|     |   | D    |     | REVISED PER ECO-21-003080  |  |  | 25OCT2021 | LN  | DH   |  |
|     |   |      |     |                            |  |  |           |     |      |  |



- 1 HOUSING: LCP, UL94V0, COLOR: BLACK.  
CONTACT: PHOSPHOR BRONZE.
- 2 FINISH: 1.27µm GOLD IN CONTACT AREA 1.27µm MIN. TIN-LEAD (93/7) ON PCB TAIL OVER 2.54µm MIN. NICKEL OVER ALL.
- 3 PLATED THROUGH HOLE PER 114-13056, FIGURE 4
- 4 ADDITIONAL CONNECTOR-SIDE KEEPOUT AREA REQUIRED IF CONNECTOR-SIDE EXTRACTION TOOL IS TO BE USED.
- 5 FINISH: 1.27µm MIN GOLD IN CONTACT AREA, 0.50µm MIN TIN ON PCB TAIL OVER 2.54µm MIN. NICKEL OVER ALL.
- 6 FINISH: 1.27µm GOLD IN CONTACT AREA 1.27µm MIN. TIN-LEAD (60/40) ON PCB TAIL OVER 2.54µm MIN. NICKEL OVER ALL.

|                                                                                                                                                                                                       |           |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------|
| JURISDICTION                                                                                                                                                                                          | EAR       |
| CLASSIFICATION                                                                                                                                                                                        | EAR99     |
| DATE OF MARKING                                                                                                                                                                                       | 17FEB2022 |
| THIS DOCUMENT CONTAINS CONTROLLED TECHNICAL DATA SUBJECT TO THE EXPORT ADMINISTRATION REGULATIONS (EAR). VIOLATIONS OF THESE EXPORT LAWS AND REGULATIONS ARE SUBJECT TO CIVIL AND CRIMINAL PENALTIES. |           |

|                                        |  |                                  |  |  |
|----------------------------------------|--|----------------------------------|--|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN<br>K. MILLER<br>28SEP2011    |  |  |
| DIMENSIONS:<br>mm                      |  | CHK<br>K. THACKSTON<br>28SEP2011 |  |  |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | APVD<br>M. McALONIS<br>11SEP2012 |  |  |
| 0 PLC ±.5                              |  | PRODUCT SPEC                     |  |  |
| 1 PLC ±0.13                            |  | 108-2072                         |  |  |
| 2 PLC ±.                               |  | APPLICATION SPEC                 |  |  |
| 3 PLC ±.                               |  | 114-13056                        |  |  |
| 4 PLC ±.                               |  | WEIGHT                           |  |  |
| ANGLES ±1°                             |  | 6.35g                            |  |  |
| FINISH                                 |  | Customer Drawing                 |  |  |
| SEE TABLE                              |  | SCALE                            |  |  |
|                                        |  | 4:1                              |  |  |
|                                        |  | SHEET                            |  |  |
|                                        |  | 1                                |  |  |
|                                        |  | OF                               |  |  |
|                                        |  | 1                                |  |  |
|                                        |  | REV                              |  |  |
|                                        |  | D                                |  |  |