




THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 19

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DS

-

P

LTR

DESCRIPTION

DATE

DWN

APVD

A

RELEASED

12.MAR'12

DG

HG


B

REVISED (ECR-13-018505)

26.NOV'13

DG

HG



3D VIEW
SCALE 1:1

DESCRIPTION

HYB 12P HEADER ASSY

ASSY P/N

2109224-2

5	TIN	COPPER ALLOY	.025 TAB S	2
4	TIN	COPPER ALLOY	.025 TAB L	2
3	TIN	COPPER ALLOY	.110 TAB SHORT	4
2	TIN	COPPER ALLOY	.110 TAB LONG	4
1	BLACK	PA6T-GF15	HEADER HSG	1
NO.	COLOR/FINISH	MATERIAL	DESCRIPTION	QTY

NOTE

1. GENERAL TOLERANCE: ± 0.3 , $\pm 3^\circ$
2. APPLICABLE COUNTER PART (PLUG) P/N: 2109220-X
3. INTERFACE DRAWING SEE SHEET 2 of 2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

DG JEONG

CHK

KT LIM

APVD

HG CHO

PRODUCT SPEC

-

APPLICATION SPEC

-


WEIGHT

-

CUSTOMER DRAWING

DIMENSIONS:

mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED

0 PLC $\pm$
1 PLC $\pm$
2 PLC $\pm$
3 PLC $\pm$
4 PLC $\pm$
ANGLES $\pm$

FINISH

-

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2109224


-

SCALE 1:1

SHEET 1

OF 2

REV B



THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 19

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1 of 2

P.C.B. LAY OUT

NOTE

1. GENERAL TOLERANCE: ± 0.15 , $\pm 1^\circ$
2. APPLICABLE P.C.B. THICKNESS: 1.6mm

ASSEMBLED LAY OUT

SECTION A-A

SECTION B-B

NOTE

1. GENERAL TOLERANCE: ± 0.15 , $\pm 1^\circ$
2. DO NOT PERMIT AS FOLLOW
; PARTING LINE, PORE, BURR AND OTHER DEFECTS
3. THIS AREA MUST BE POLISHED.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity

NAME

.025/.110 12P HEADER ASSY

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2109224

SCALE

1:1

SHEET

2

OF

2

REV

B