

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER ECO-21-000028	04JAN2021	DW	JH
	A1	REVISED PER ECN-24-252773	09JAN2024	DW	JH
	A2	REVISED PER ECN-25-323254	23MAY2025	DW	VK
	B	REVISED PER ECN-25-328175	20JUN2025	DW	VK

NOTES : UNLESS OTHERWISE SPECIFIED


- FABRICATE TO MEET IPC - 6012, CLASS 2.
INSPECT TO MEET IPC - A - 600, CLASS 2.
- MATERIAL :
 - A. PCB : FR4 + ADHESIVE
 - B. ADHESIVE WITH LINER ON THE BACK SIDE, REMOVE LINER TO APPLY.
 - C. CABLE WITH CONNECTOR
- FINISH : SOLDERMASK BOTH SIDES, ORANGE
- GENERAL TOLERANCES : ± 0.20
- PACKING : SECURELY SHRINK WRAPPED, VACUUM PACKED OR BAGS PACKAGED IN BULK.
- CONSULT TE CONNECTIVITY DATA SHEET DS2108857.



MINIMUM IDENTIFICATION INCLUDES

- TE LOGO, TE P/N
- WORD REV., FOLLOWED BY THE LATEST REVISION LETTER, AS SHOWN.
- 4 DIGITS DATE CODE : FIRST 2 DIGITS FOR THE WEEK CODE
AND THE 2 DIGITS FOR THE YEAR CODE.
OTHERS : SPECIFIC TE INTERNAL USE ONLY.

MHF 4L (CABLE O.D 0.81)	300.00	1-2108857-3
	250.00	2108857-9
	200.00	2108857-8
	150.00	2108857-7
	100.00	2108857-6
	50.00	2108857-5
MHF 1 (CABLE O.D 1.37)	300.00	1-2108857-2
	250.00	1-2108857-1
	200.00	2108857-4
	150.00	2108857-3
	100.00	2108857-2
	50.00	2108857-1
"C" CONN. TYPE	A (mm)	PART NUMBER



DOUBLE-SIDED FOAM TAPE	ADHESIVE	4
UV CURING EPOXY	GLUING	3
COAXIAL CABLE & CONN.	CABLE ASS'Y	2
FR4	PCB ANTENNA	1
MATERIAL	NAME	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC $\pm$
	1 PLC $\pm$
	2 PLC $\pm$
	3 PLC $\pm$
	4 PLC $\pm$
	ANGLES $\pm$
MATERIAL	FINISH
-	-
-	-

DWN	DW.PARK	09DEC2020
CHK	H.SHIN	09DEC2020
APVD	JH.KIM	09DEC2020
PRODUCT SPEC	108-61449	
APPLICATION SPEC	-	
WEIGHT	-	
CUSTOMER DRAWING	SCALE	3:1

TE Connectivity			
NAME PCB ANTENNA, CABLE, Wi-Fi 6E TRIPLE BAND			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2108857	-
SHEET 1 OF 1		REV B	