




P	LTR	DESCRIPTION	DATE	DWN	APVD
U		ECN-23-XXXXXX; DRW REG W/CREO	27JUL2023	DR	JW
V		REV PER ECN-24-296130	02DEC2024	JAB	MN



- NOTES:
- MATES WITH TEC P/N 211159-11N AMPLIMITE CONNECTOR ASSEMBLIES ONLY
 - APPROVED CRIMP TOOLING: DANIELS CRIMP TOOL P/N M300-BT, DANIELS POSITIONER P/N SP689, STRIP LENGHT = .375 [9.53], #8 AWG SETTING 7, #10 AWG SETTING 6.
NOTE: USE OF ANY UNAPPROVED TOOLING WILL RESULT IN CRIMPED TERMINATIONS THAT ARE NOT QUALIFIED
 - WIRE BARREL ACCEPTS #8 -#10 AWG STRANDED WIRE
- 4 RETENTION CLIP DIAMETER TO BE MEASURED WITH RING GAGE
- 5 FINISH:
CONTACT: GOLD PLATE .000050 [.00127] MIN THK PER ASTM-B-488 OVER
NICKEL UNDERPLATE .000050 [.00127] MIN THK PER PER QQ-N-290
RETENTION CLIP: NICKEL PLATE .000050 [.00127] MIN THK PER PER QQ-N-290
- 6 RESTRICTED PART NUMBER

6	-	.136 [3.45]	.185 [4.70]	10	1-211161-2
6	-	.181 [4.60]	.230 [5.84]	8	1-211161-1
5	.136 [3.45]	.185 [4.70]	10	211161-2	
5	.181 [4.60]	.230 [5.84]	8	211161-1	
FINISH		øB	øA	WIRE SIZE [AWG]	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C. THOMAS 06SEPT2000	TE Connectivity		
DIMENSIONS: IN [MM]		CHK CHAD BAKER 06SEPT2000	NAME CONTACT ASSY, SOCKET CRIMP TYPE, WIRE SIZE #8 & #10 AWG		
		APVD CHAD BAKER 06SEPT2000			
		PRODUCT SPEC			
		APPLICATION SPEC			
MATERIAL		SIZE CAGE CODE DRAWING NO	RESTRICTED TO		
-		A 00779 C=211161	-		
-		CUSTOMER DRAWING	SCALE 10:1	SHEET 1 OF 1	REV V