

D

C

B

A





D

C

B

A

REVISIONS					
P	T	LTR	DESCRIPTION	DATE	DWN APVD
	T		REVISED PER ECR-24-213594	02JUL2024	RK FJS



RECOMMENDED PC BOARD LAYOUT

1.75 [.069]	32.36 [1.274]	1.40-1.98 [.055-.078]
2.74 [.108]	30.05 [1.183]	0.79-1.40 [.031-.055]
B	A	PANEL THICKNESS

- 1 PANEL CUTOUT FOR REAR MOUNTED PIN BLOCK.
- 2 SEAMS OF ALL PINS TO BE ORIENTED TOWARD HOLE X SIDE.
- 3 POLYESTER, BLACK.
- 4 0.76µm [.000030] MIN PRECIOUS METAL PLATE FOR A LENGTH OF 6.35 [.250] MIN FROM MATING END, GOLD FLASH ON REMAINDER, BOTH OVER 1.27µm [.000050] MIN NICKEL PER QQ-N-290.
- 5 2.54µm [.000100] MIN TIN-LEAD PER MIL-T-10727 OVER 2.54µm [.000100] MIN COPPER PER MIL-C-14550.
- 6 2.54µm [.000100] MIN TIN PER MIL-T-10727 OVER 2.54µm [.000100] MIN COPPER PER MIL-C-14550.
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	5	4	5.59 [.220]	211580-6
	6	4	3.56 [.140]	211580-5
	6	4	19.76 [.778]	211580-4
OBSOLETE	5	4	3.56 [.140]	211580-3
OBSOLETE	5	4	19.76 [.778]	211580-2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 09/09/92	L.SIPE	
DIMENSIONS: mm [INCHES]		CHK 10-15-92	R.STONE	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME	
0. PLC ± -		PRODUCT SPEC	CONNECTOR BLOCK FOR PINS WITH FEMALE JACKSCREW THREAD, 62 POSN, METRIMATE	
1. PLC ± -		APPLICATION SPEC		
2. PLC ± 0.13 [.005]		WEIGHT -		
3. PLC ± 0.013 [.0005]		CUSTOMER DRAWING		
4. PLC ± -		SCALE 2:1	SHEET 1 OF 1	
ANGLES ± -		REV		
FINISH				