

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 19 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED<ECR-14-011552>	28.MAY.'15	SJ	HG
	C	REVISED<ECR-15-007719>	01.JUN.'15	SH	HG
	D	REVISED<ECR-17-016014>	31.OCT.'17	SH	YJ

NOTE

1. GENERAL TOLERANCE: ±0.3, ±3°


△ RETAINER IS PRE-LOCKING

3. APPLICABLE TERMINAL: SEE TABLE




4. APPLICABLE CLIP : P/N :1-1897255-2

5. MATING P/N : 2109272



TYPE	P/N	SQ
.025TH	2005098-1	0.22
	2005154-1	0.3~0.5
.060	2109005-1	0.22~0.3
	2109005-2	0.5~0.75
	2109005-3	0.85~1.25
.250	964304-1	0.5~1.0
	964306-1	1.0~2.5
	964308-1	2.5~4.0



3D VIEW
SCALE 1:1



SECTION E-E



①	2	NATURAL	PBT	DBL FOR 22P CAP ASM	1
	1	NATURAL	PBT	025/060/250 22P HYB CAP HSG	1
	NO.	COLOR	MATERIAL	DESCRIPTION	Q'TY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SH JANG		TE Connectivity							
DIMENSIONS: mm		CHK DG JEONG									
		TOLERANCES UNLESS OTHERWISE SPECIFIED		NAME -							
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC -							
MATERIAL -		FINISH -		APPLICATION SPEC -							
				WEIGHT -							
CUSTOMER DRAWING				SIZE A3		CAGE CODE -		DRAWING NO C-2109275		RESTRICTED TO -	
				SCALE 1:1		SHEET 1 OF 1		REV D			