

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

LOC

DIST

REVISIONS

© COPYRIGHT BY - Taipei, Taiwan

ALL RIGHTS RESERVED.

HY

P

LTR

DESCRIPTION

DATE

DWN

APVD


A

FIRST ISSUE

12,AUG,11'

SW

WW




TEST ALL PRODUCTS AS BELOW:  
 100% OPEN & SHORT TEST.  
 CONTACT RESISTANCE:3 OHM MAX.  
 INSULATION RESISTANCE:10 MOHM MIN.  
 WITHSTADING VOLTAGE 300V(DC) 0.1sec.

CONN.1	PIN ASSIGNMENT	CONN.2
	COLOR	
1	RED	1
2	WHITE	2
3	GREEN	3
4	BLACK	4
5	BLUE	8
6	YELLOW	9
7	DRAIN WIRE	7
8	PURRLE	5
9	ORANGE	6
SHELL	BRAID	SHELL

1-2117156-0	1000±20
PART NUMBER	L

AR	MR	COPPER FOIL TAPE	4
AR	KG	OVER MOLDED PVC, COLOR: BLACK	3
2	PC	USB 3.0 PLUG, A TYPE, AU PLATED 30u" FOR CONTACT AREA	2
AR	MR	USB 3.0 CABLE, OD=4.5 (1P*32#+D+AL+Mylar)*2C+1P*32#+2C*26#+AL+B /UL20276	1
QTY	U/M	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WU 12,AUG,2011	 TE Connectivity	
DIMENSIONS: MM		CHK CP. ONG 12,AUG,2011		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± 3'		APVD W. WANG 12,AUG,2011	NAME	
MATERIAL SEE NOTE		FINISH SEE NOTE	PRODUCT SPEC QUALIFICATION TEST REPORT WEIGHT CUSTOMER DRAWING	
		SIZE A3	CAGE CODE 00779	DRAWING NO C=2117156
		RESTRICTED TO —		SCALE — SHEET 1 OF 2 REV A

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- . - .

© COPYRIGHT - BY - Taipei, Taiwan

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

HY

-


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	FIRST ISSUE	12,AUG,11'	SW	WW

TEST ALL PRODUCTS AS BELOW:  
 100% OPEN & SHORT TEST.  
 CONTACT RESISTANCE:3 OHM MAX.  
 INSULATION RESISTANCE:10 MOHM MIN.  
 WITHSTADING VOLTAGE 300V(DC) 0.1sec.

CONN.1	PIN ASSIGNMENT	CONN.2
1	RED	1
2	WHITE	2
3	GREEN	3
4	BLACK	4
5	BLUE	8
6	YELLOW	9
7	DRAIN WIRE	7
8	PURRLE	5
9	ORANGE	6
SHELL	BRAID	SHELL

2-2117156-0	2000±20
1-2117156-5	1500±20
PART NUMBER	L

AR	MR	DESCRIPTION	ITEM
		COPPER FOIL TAPE	4
		OVER MOLDED PVC, COLOR: BLACK	3
2	PC	USB 3.0 PLUG, A TYPE, AU PLATED 30u" FOR CONTACT AREA	2
AR	MR	USB 3.0 CABLE, OD=5.5 (1P*28#+D+AL+Mylar)*2C+1P*28#+2C*24#+AL+B /UL20276	1
QTY	U/M		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WU 12,AUG,2011	 TE Connectivity	
DIMENSIONS: MM		CHK CP. ONG 12,AUG,2011		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± - ± 3' ANGLES		APVD W. WANG 12,AUG,2011	NAME	
MATERIAL SEE NOTE		FINISH SEE NOTE	PRODUCT SPEC	
		QUALIFICATION TEST REPORT	USB 3.0 A to A Cable Ass'y	
		WEIGHT	SIZE A3	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO C=2117156	RESTRICTED TO -
		SCALE -	SHEET 2 OF 2	REV A

1470-19 (3/11)