




LOC	DIST	REVISIONS					
		P	LTN	DESCRIPTION	DATE	DWN	APVD
AD	00	A		CREATED BY AUTOMATION PROGRAM	10MAY2011	RKC	JE



NOTCH DESIGNATES ROW A



- 1 MATERIAL:  
HOUSING: LCP, GLASS FILLED, UL94V-0.  
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:  
30µ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:  
30µ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD ON PCB TAILS, NICKEL OVERALL.
- 4. SCREWS PACKAGED IN END OF PACKAGING TUBE.
- 5 FOR GROUNDED GUIDE PIN USE Ø3.56±0.08 PTH, Ø3.66 DRILL, AND Ø6.5 PAD.
- 6. KEYING PIN SHOWN IN POSITION A, SEE KEYING CHART ON SHEET 2 FOR OTHER POSITIONS.




Ø3.56±0.08  
Ø0.15 UNPLATED SCREW HOLE

180X Ø0.46±0.05 PLATED THRU HOLE


180X Ø0.55±0.013 DRILL HOLE  
Ø0.10

LEFT GUIDED BACKPLANE HOLE PATTERN (CONNECTOR SIDE)



1.4 TAIL LENGTH

1.00 MINIMUM BOARD THICKNESS



SECTION A-A


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COELLO 09MAY2011	TE Connectivity
DIMENSIONS: mm		CHK J. EARY 09MAY2011	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. EARY 09MAY2011	NAME: IMPACT, 5 PAIR, 12 COLUMN, HEADER LEFT GUIDED, RIGHT END WALL SIGNAL MODULE, 0.46 PTH
0 PLC ±0.25		PRODUCT SPEC	
1 PLC ±0.13		APPLICATION SPEC	SIZE: CAGE CODE DRAWING NO: A100779C=2110181 WEIGHT: - CUSTOMER DRAWING
2 PLC ±0.10		RESTRICTED TO	
3 PLC ±0.08		SCALE: 5:1	SHEET 1 OF 2 REV A
4 PLC ±0.05			
ANGLES ±0.5			
FINISH: SEE TABLE			

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20  
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
AD	00	P	LTN	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1		-	-

3	H	5.5	8-2110181-6
3	H	4.9	8-2110181-5
3	H	4.5	8-2110181-4
2	H	5.5	8-2110181-3
2	H	4.9	8-2110181-2
2	H	4.5	8-2110181-1
3	G	5.5	7-2110181-6
3	G	4.9	7-2110181-5
3	G	4.5	7-2110181-4
2	G	5.5	7-2110181-3
2	G	4.9	7-2110181-2
2	G	4.5	7-2110181-1
3	F	5.5	6-2110181-6
3	F	4.9	6-2110181-5
3	F	4.5	6-2110181-4
2	F	5.5	6-2110181-3
2	F	4.9	6-2110181-2
2	F	4.5	6-2110181-1
3	E	5.5	5-2110181-6
3	E	4.9	5-2110181-5
3	E	4.5	5-2110181-4
2	E	5.5	5-2110181-3
2	E	4.9	5-2110181-2
2	E	4.5	5-2110181-1
3	D	5.5	4-2110181-6
3	D	4.9	4-2110181-5
3	D	4.5	4-2110181-4
2	D	5.5	4-2110181-3
2	D	4.9	4-2110181-2
2	D	4.5	4-2110181-1
3	C	5.5	3-2110181-6
3	C	4.9	3-2110181-5
3	C	4.5	3-2110181-4
2	C	5.5	3-2110181-3
2	C	4.9	3-2110181-2
2	C	4.5	3-2110181-1
3	B	5.5	2-2110181-6
3	B	4.9	2-2110181-5
3	B	4.5	2-2110181-4
2	B	5.5	2-2110181-3
2	B	4.9	2-2110181-2
2	B	4.5	2-2110181-1
3	A	5.5	1-2110181-6
3	A	4.9	1-2110181-5
3	A	4.5	1-2110181-4
2	A	5.5	1-2110181-3
2	A	4.9	1-2110181-2
2	A	4.5	1-2110181-1
3	-	5.5	2110181-6
3	-	4.9	2110181-5
3	-	4.5	2110181-4
2	-	5.5	2110181-3
2	-	4.9	2110181-2
2	-	4.5	2110181-1
FINISH	KEY POSITION	DIM M	PART NUMBER

REFER TO WWW.TE.COM FOR PRODUCT AVAILABILITY



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COELLO 09MAY2011	<b>TE</b> Connectivity
DIMENSIONS: mm		CHK J. EARY 09MAY2011	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. EARY 09MAY2011	
0 PLC ±0.25	1 PLC ±0.13	2 PLC ±0.13	NAME IMPACT, 5 PAIR, 12 COLUMN, HEADER LEFT GUIDED, RIGHT END WALL SIGNAL MODULE, 0.46 PTH
3 PLC ±0.13	4 PLC ±0.13	ANGLES ±0.13	PRODUCT SPEC
MATERIAL	FINISH SEE TABLE	WEIGHT	APPLICATION SPEC
			SIZE CAGE CODE DRAWING NO RESTRICTED TO
			A100779C=2110181
			CUSTOMER DRAWING SCALE 5:1 SHEET 2 OF 2 REV A