



REVISIONS				
P	LTN	DESCRIPTION	DATE	APVD
M		ECN-23-225270	07AUG2023	DR JHW

Ø.067[1.70]
WIRE BARREL
INSIDE DIAMETER
NOMINAL DEPTH .350 [8.89]



- MATES WITH TEC P/N 212014 IN AMPLIMITE CONNECTOR ASSEMBLIES ONLY
 - PART TO BE USED WITH 16-18AWG STRANDED WIRE ONLY
 - APPROVED CRIMP TOOLING: DANIELS CRIMP TOOL P/N FT8, DANIELS POSITIONER P/N TP731, STRIP LENGTH=.375 [9.53]
CRIMP SETTING: 16AWG - SETTING 8
CRIMP SETTING: 18AWG - SETTING 6
- $\Delta 4$ RETENTION CLIP DIAMETER TO BE MEASURED WITH RING GAGE
- $\Delta 5$ FINISH: CONTACT: GOLD PLATE .000050 [0.00127] MIN THK PER ASTM-B-488 OVER NICKEL PLATE .000050 [0.00127] MIN THK PER QQ-N-290
- $\Delta 6$ RESTRICTED PART NUMBER

$\Delta 6$	1-212013-1
--	212013-1
NOTES	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: IN [MM]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN C.C. THOMAS 10NOV2000	CHK D. MILLER 10NOV2000	APVD D. MILLER 10NOV2000	NAME CONTACT, ASSEMBLY, SIZE 8, PIN #16-18 AWG
	0 PLC ±.1 1 PLC ±.1 2 PLC ±.02 3 PLC ±.005 4 PLC ±.0005 ANGLES ±.1	PRODUCT SPEC	APPLICATION SPEC	SIZE A	CAGE CODE 00779
MATERIAL SEE NOTES	FINISH SEE NOTES	WEIGHT	CUSTOMER DRAWING	DRAWING NO 212013-C	RESTRICTED TO
				SCALE 5:1	SHEET 1 OF 1

TE Connectivity