






REVISIONS				
P.	LTN.	DESCRIPTION	DATE	APVD.
B		REVISED PER ECO-14-000933	29JAN2014	AP DD

- △ MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- △ FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN ON PCB TAILS, NICKEL OVERALL.
- △ FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD ON PCB TAILS, NICKEL OVERALL.
- 4. SCREWS PACKAGED IN END OF PACKAGING TUBE.
- △ FOR GROUNDED GUIDE PIN USE Ø3.56±0.08 PTH, Ø3.66 DRILL, AND Ø6.5 PAD.
- 6. KEYING PIN SHOWN IN POSITION A, SEE KEYING CHART ON SHEET 2 FOR OTHER POSITIONS.

NOTCH DESIGNATES ROW A




LEFT GUIDED BACKPLANE HOLE PATTERN (CONNECTOR SIDE)



THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: RKC 09MAY2011	TE Connectivity
DIMENSIONS: mm		CHK: J. EARY 09MAY2011	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: J. EARY 09MAY2011	NAME: IMPACT, 5 PAIR, 12 COLUMN, HEADER LEFT GUIDED, RIGHT END WALL SIGNAL MODULE, 0.39 PTH
0 PLC	±	PRODUCT SPEC	APPLICATION SPEC
1 PLC	±0.25	SIZE	CAGE CODE DRAWING NO
2 PLC	±0.13	WEIGHT	RESTRICTED TO
3 PLC	±	A100779C=2110182	
4 PLC	±	CUSTOMER DRAWING	
ANGLES	±	SCALE 5:1 SHEET 1 OF 2 REV B	

REVISIONS				
P.	LTN	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-

3	H	5.5	8-2110182-6
3	H	4.9	8-2110182-5
3	H	4.5	8-2110182-4
2	H	5.5	8-2110182-3
2	H	4.9	8-2110182-2
2	H	4.5	8-2110182-1
3	G	5.5	7-2110182-6
3	G	4.9	7-2110182-5
3	G	4.5	7-2110182-4
2	G	5.5	7-2110182-3
2	G	4.9	7-2110182-2
2	G	4.5	7-2110182-1
3	F	5.5	6-2110182-6
3	F	4.9	6-2110182-5
3	F	4.5	6-2110182-4
2	F	5.5	6-2110182-3
2	F	4.9	6-2110182-2
2	F	4.5	6-2110182-1
3	E	5.5	5-2110182-6
3	E	4.9	5-2110182-5
3	E	4.5	5-2110182-4
2	E	5.5	5-2110182-3
2	E	4.9	5-2110182-2
2	E	4.5	5-2110182-1
3	D	5.5	4-2110182-6
3	D	4.9	4-2110182-5
3	D	4.5	4-2110182-4
2	D	5.5	4-2110182-3
2	D	4.9	4-2110182-2
2	D	4.5	4-2110182-1
3	C	5.5	3-2110182-6
3	C	4.9	3-2110182-5
3	C	4.5	3-2110182-4
2	C	5.5	3-2110182-3
2	C	4.9	3-2110182-2
2	C	4.5	3-2110182-1
3	B	5.5	2-2110182-6
3	B	4.9	2-2110182-5
3	B	4.5	2-2110182-4
2	B	5.5	2-2110182-3
2	B	4.9	2-2110182-2
2	B	4.5	2-2110182-1
3	A	5.5	1-2110182-6
3	A	4.9	1-2110182-5
3	A	4.5	1-2110182-4
2	A	5.5	1-2110182-3
2	A	4.9	1-2110182-2
2	A	4.5	1-2110182-1
3	-	5.5	2110182-6
3	-	4.9	2110182-5
3	-	4.5	2110182-4
2	-	5.5	2110182-3
2	-	4.9	2110182-2
2	-	4.5	2110182-1
FINISH	KEY POSITION	DIM M	PART NUMBER



REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: RKC 09MAY2011 CHK: J. EARY 09MAY2011 APVD: J. EARY 09MAY2011	TE Connectivity
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.25 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±	PRODUCT SPEC APPLICATION SPEC WEIGHT CUSTOMER DRAWING	
MATERIAL	SEE TABLE	SIZE: CAGE CODE: DRAWING NO: A100779C=2110182 RESTRICTED TO: -	NAME: IMPACT, 5 PAIR, 12 COLUMN, HEADER LEFT GUIDED, RIGHT END WALL SIGNAL MODULE, 0.39 PTH
SCALE: 5:1		SHEET 2 OF 2	REV B