




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		A	CREATED BY AUTOMATION PROGRAM	02MAY2011	RKC	JE
			A1	REVISED PER ECN-24-252036	20MAR2024	AP	RS





- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.



252X $\varnothing 0.39 \pm 0.05$
 $\varnothing \varnothing 0.10$
PLATED THRU HOLE

UNGUIDED
BACKPLANE HOLE PATTERN
(CONNECTOR SIDE)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COELLO 02MAY2011	 TE Connectivity		
DIMENSIONS:		CHK J. EABY 02MAY2011			
mm		APVD J. EABY 02MAY2011	NAME IMPACT, 6 PAIR, 14 COLUMN, HEADER UNGUIDED, OPEN END WALL SIGNAL MODULE, 0.39 PTH		
		PRODUCT SPEC			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APPLICATION SPEC	SIZE CAGE CODE DRAWING NO. RESTRICTED TO		
		0 PLC ±			
MATERIAL	FINISH	1 PLC ±0.25	A100779C=2132012		
		2 PLC ±0.13			
	SEE TABLE	3 PLC ±	CUSTOMER DRAWING		
		4 PLC ±			
		ANGLES	SCALE 5:1 SHEET 1 OF 2 REV A1		
		FINISH			

LOC		DIST		REVISIONS					
AD	00	P	LTR	DESCRIPTION			DATE	DWN	APVD
			-	SEE SHEET 1			-	-	-

	5.5	2132012-6	OBSOLETE
	4.9	2132012-5	
	4.5	2132012-4	
	5.5	2132012-3	
	4.9	2132012-2	OBSOLETE
	4.5	2132012-1	
FINISH	DIM M	PART NUMBER	

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN -	02MAY2011		TE Connectivity	
		CHK J. EABY	02MAY2011			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
mm		0 PLC ±.25 1 PLC ±0.25 2 PLC ±0.13 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH		IMPACT, 6 PAIR, 14 COLUMN, HEADER UNGUIDED, OPEN END WALL SIGNAL MODULE, 0.39 PTH		
		PRODUCT SPEC		SIZE		
		APPLICATION SPEC		CAGE CODE		
MATERIAL		WEIGHT		DRAWING NO		
-		-		A100779C=2132012		
CUSTOMER DRAWING				SCALE	5:1	
				SHEET	2	
				OF	2	
				REV	A1	