




LOC	DIST	REVISIONS			
AD	00	REV	DATE	BY	APPV
		A	10MAY2011	RKC	JE



NOTCH DESIGNATES ROW A





- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30µ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30µ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD ON PCB TAILS, NICKEL OVERALL.
- 4. SCREWS PACKAGED IN END OF PACKAGING TUBE.
- 5 FOR GROUNDED GUIDE PIN USE $\varnothing 3.56 \pm 0.08$ PTH, $\varnothing 3.66$ DRILL, AND $\varnothing 6.5$ PAD.
- 6. KEYING PIN SHOWN IN POSITION A, SEE KEYING CHART ON SHEET 2 FOR OTHER POSITIONS.



- PIN A1
- GROUND HOLE REF
- SIGNAL HOLES REF
- ROW A
- ROW B
- ROW C
- ROW D
- ROW E
- ROW F
- ROW G
- ROW H
- ROW J
- ROW K
- ROW L
- ROW M
- ROW N
- ROW O
- ROW P

180X $\varnothing 0.46 \pm 0.05$ PLATED THRU HOLE
 180X $\varnothing 0.55 \pm 0.013$ DRILL HOLE $\varnothing 0.10$
 $\varnothing 3.56 \pm 0.08$ UNPLATED SCREW HOLE

RIGHT GUIDED BACKPLANE HOLE PATTERN (CONNECTOR SIDE)



SECTION A-A


1.00 MINIMUM BOARD THICKNESS

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN R. COELLO 09MAY2011	TE Connectivity
DIMENSIONS: mm		CHK J. EARY 09MAY2011	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPV J. EARY 09MAY2011	
0 PLC ± 1 PLC ±0.25 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±		NAME IMPACT, 5 PAIR, 12 COLUMN, HEADER RIGHT GUIDED, OPEN END WALL SIGNAL MODULE, 0.46 PTH SIZE CAGE CODE DRAWING NO. RESTRICTED TO A100779C=2110183 WEIGHT CUSTOMER DRAWING SCALE 5:1 SHEET 1 OF 2 REV A	

LOC	DIST	P	LTN	DESCRIPTION	DATE	DWN	APVD
AD	00	-	-	SEE SHEET 1	-	-	-

3	H	5.5	8-2110183-6
3	H	4.9	8-2110183-5
3	H	4.5	8-2110183-4
2	H	5.5	8-2110183-3
2	H	4.9	8-2110183-2
2	H	4.5	8-2110183-1
3	G	5.5	7-2110183-6
3	G	4.9	7-2110183-5
3	G	4.5	7-2110183-4
2	G	5.5	7-2110183-3
2	G	4.9	7-2110183-2
2	G	4.5	7-2110183-1
3	F	5.5	6-2110183-6
3	F	4.9	6-2110183-5
3	F	4.5	6-2110183-4
2	F	5.5	6-2110183-3
2	F	4.9	6-2110183-2
2	F	4.5	6-2110183-1
3	E	5.5	5-2110183-6
3	E	4.9	5-2110183-5
3	E	4.5	5-2110183-4
2	E	5.5	5-2110183-3
2	E	4.9	5-2110183-2
2	E	4.5	5-2110183-1
3	D	5.5	4-2110183-6
3	D	4.9	4-2110183-5
3	D	4.5	4-2110183-4
2	D	5.5	4-2110183-3
2	D	4.9	4-2110183-2
2	D	4.5	4-2110183-1
3	C	5.5	3-2110183-6
3	C	4.9	3-2110183-5
3	C	4.5	3-2110183-4
2	C	5.5	3-2110183-3
2	C	4.9	3-2110183-2
2	C	4.5	3-2110183-1
3	B	5.5	2-2110183-6
3	B	4.9	2-2110183-5
3	B	4.5	2-2110183-4
2	B	5.5	2-2110183-3
2	B	4.9	2-2110183-2
2	B	4.5	2-2110183-1
3	A	5.5	1-2110183-6
3	A	4.9	1-2110183-5
3	A	4.5	1-2110183-4
2	A	5.5	1-2110183-3
2	A	4.9	1-2110183-2
2	A	4.5	1-2110183-1
3	-	5.5	2110183-6
3	-	4.9	2110183-5
3	-	4.5	2110183-4
2	-	5.5	2110183-3
2	-	4.9	2110183-2
2	-	4.5	2110183-1
FINISH	KEY POSITION	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COELLO 09MAY2011	TE Connectivity														
DIMENSIONS: mm		CHK J. EARY 09MAY2011															
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. EARY 09MAY2011															
<table border="1"> <tr><td>0 PLC</td><td>±</td></tr> <tr><td>1 PLC</td><td>±0.25</td></tr> <tr><td>2 PLC</td><td>±0.13</td></tr> <tr><td>3 PLC</td><td>±</td></tr> <tr><td>4 PLC</td><td>±</td></tr> <tr><td>ANGLES</td><td>±</td></tr> <tr><td>FINISH</td><td>±</td></tr> </table>		0 PLC	±	1 PLC	±0.25	2 PLC	±0.13	3 PLC	±	4 PLC	±	ANGLES	±	FINISH	±	NAME IMPACT, 5 PAIR, 12 COLUMN, HEADER RIGHT GUIDED, OPEN END WALL SIGNAL MODULE, 0.46 PTH	RESTRICTED TO
0 PLC	±																
1 PLC	±0.25																
2 PLC	±0.13																
3 PLC	±																
4 PLC	±																
ANGLES	±																
FINISH	±																
MATERIAL: -		PRODUCT SPEC: -	SIZE: A100779														
SEE TABLE		APPLICATION SPEC: -	CAGE CODE: C=2110183														
CUSTOMER DRAWING		WEIGHT: -	SCALE: 5:1														
			SHEET 2 OF 2														
			REV A														