



D


C

B

A



213420-3 SHOWN



- DUST COVER IS INSTALLED FOR SHIPPING.
- KEYING SHOWN IN POSITION "01" FOR ILLUSTRATION ONLY. CONNECTORS SHIPPED WITH KEYING INSTALLED IN POSITION PER TABLE.

COMPONENT	MATERIAL	FINISH
SHELL	DIE CAST ALUMINUM PER ASTM-B-85	CHEMICAL CONVERSION COATING PER MIL-C-5541, CLASS 1A
INSERT RETENTION PLATES	ALUMINUM ALLOY PER ASTM-B-209	CHEMICAL CONVERSION COATING PER MIL-C-5541, CLASS 1A
SCREWS AND LOCKWASHERS	STEEL OR STAINLESS STEEL	CHROMATE OVER ZINC OR PASSIVATED
POLARIZING POSTS	ZINC ALLOY PER ASTM-B-86	ELECTROLESS NICKEL PER MIL-C-26074 CLASS 4, GRADE B
POLARIZING POST RETAINING PLATE	ALUMINUM ALLOY PER ASTM-B-209	BLUE ANODIZED PER MIL-A-8625
ALL INSERTS	THERMOSET	—
EMI SPRINGS	BERYLLIUM COPPER PER ASTN B-194	-1 & -2 CHROMATE -3 ELECTROLESS NICKEL

NO CONTACTS INCLUDED	213420-3
FOR MODULE A 211901-5 (SZ 22 CRIMP PIN CONTACT; QTY=150) FOR MODULE B 208267-4 (SZ 20 CRIMP SOCKET CONTACT; QTY=20) 222191-1 (SZ 8 TRIAX SOCKET CONTACT; QTY=4 FOR MODULE C 211901-5 (SZ 22 CRIMP PIN CONTACT; QTY=150) FOR MODULE D 211901-5 (SZ 22 CRIMP PIN CONTACT; QTY=100)	213420-1 213420-2
CONTACTS INCLUDED AND NOT INSTALLED	PART NUMBER

UNSEALED INSERTS	"31"	213420-3
SEALED INSERTS	"56"	213420-2
SEALED INSERTS	"31"	213420-1
REMARKS	KEY POSITION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 3-20-15	TE Connectivity	
DIMENSIONS: INCHES		CHK W.BERNHART 3-20-15	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD W.BERNHART 3-20-15	PRODUCT SPEC	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -		APPLICATION SPEC		
MATERIAL -		WEIGHT -		
FINISH -		SIZE A1		
CUSTOMER DRAWING		00779 213420		
SCALE NTS		SHEET 1 OF 1		
REV A		RESTRICTED TO -		