







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
J1	REVISED	PER ECR-25-240521	07APR2025	RK	JMV



PN 1-213729-2 ONLY



- 1

CAVITY IDENTIFICATION CHARACTERS ON FRONT AND REAR FACE.
- 2

NYLON, UL 94V-0 RATED, BLACK.
- 3

CONTACT BODY: 0.76um[.000030] MIN GOLD FOR LENGTH OF 5.08[.200] MIN FROM MATING END, WITH REMAINDER TO BE GOLD FLASH, BOTH OVER 1.27um[.000050] MIN NICKEL. CONTACT POST: 2.54um[.000100] MIN TIN-LEAD OVER 2.54um[.000100] MIN COPPER.
- 4

CONTACT BODY: 2.54um[.000100] MIN TIN-LEAD OVER 1.27um[.000050] MIN NICKEL. CONTACT POST: 2.54um[.000100] MIN TIN-LEAD OVER 2.54um[.000100] MIN COPPER.
- 5

CONTACT BODY: 0.76um[.000030] MIN PRECIOUS METAL PLATE FOR LENGTH OF 5.08[.200] MIN FROM MATING END, WITH REMAINDER TO BE GOLD FLASH, BOTH OVER 1.27um[.000050] MIN NICKEL. CONTACT POST: 2.54um[.000100] MIN TIN OVER 2.54um[.000100] MIN COPPER.
- 6

CONTACT BODY: 2.54um[.000100] MIN TIN OVER 1.27um[.000050] MIN NICKEL. CONTACT POST: 2.54um[.000100] MIN TIN OVER 2.54um[.000100] MIN COPPER.
- 7

PRELIMINARY PART NUMBER.
- 8

OBSOLETE PARTS
- 9

CONTACT BODY: .76um[.000030] MIN PRECIOUS METAL PLATE INTERNALLY, EXTERNAL [.000005 - .000008] OVER NICKEL (.000030-.000070) CONTACT POST: [.000100 - .000200] MATTE TIN OVER [.000050] MIN NICKEL

PRILIMINARY		3.81 ± 0.08[.150 ± .003] DIA	9	1-213729-2
	11.35[.447]	4-40 UNC, INSERT, BRASS	5	1-213729-1
7 OBSOLETE	14.22[.560]	4-40 UNC, INSERT, BRASS	5	1-213729-0
	9.35[.368]	3.81±0.08[.150±.003] DIA	5	213729-9
8 OBSOLETE	4.04[.159]	4-40UNC, INSERT, BRASS	6	213729-8
8 OBSOLETE	9.35[.368]	3.81±0.08[.150±.003] DIA	6	213729-7
	9.35[.368]	4-40UNC, INSERT, BRASS	5	213729-6
7 OBSOLETE	4.04[.159]	3.81±0.08[.150±.003] DIA	4	213729-5
8 OBSOLETE	4.04[.159]	4-40UNC, INSERT, BRASS	4	213729-4
8 OBSOLETE	9.35[.368]	3.81±0.08[.150±.003] DIA	4	213729-3
OBSOLETE	9.35[.368]	4-40UNC, INSERT, BRASS	3	213729-2
OBSOLETE	9.35[.368]	3.81±0.08[.150±.003] DIA	3	213729-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W.G.LENKER CHK R.STONE APVD	12-3-91 12-11-91	TE Connectivity	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-10024	NAME	SIZE	RESTRICTED TO
	0. PLC ± - 1. PLC ± - 2. PLC ± 0.25[.010] 3. PLC ± - 4. PLC ± - ANGLES ± -	APPLICATION SPEC 114-10004	RECEPTACLE ASSEMBLY, POSTED, SERIES 1, REVERSE SEX, CPC	CAGE CODE	
MATERIAL RECEPTACLE: 2	FINISH -	WEIGHT -	A100779C=213729	DRAWING NO	
CONTACT: BRASS		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 1	REV J1