


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
G		REVISED PER ECR-24-213594	02JUL2024	RK	FJS



0.76μm[.000030] MIN GOLD FOR A LENGTH OF 5.46[.215] MIN FROM MATING END, 3.81μm[.000150] MIN TIN-LEAD ON OPPOSITE END FOR A LENGTH OF 5.08[.200] MIN, BOTH OVER 1.27μm[.000050] MIN NICKEL.

AMP PART NUMBER AND DATE CODE MARKED IN THIS AREA.

0.76μm[.000030] MIN GOLD FOR A LENGTH OF 7.62[.300] MIN FROM MATING END, 3.81μm[.000150] MIN TIN-LEAD ON OPPOSITE END FOR A LENGTH OF 5.08[.200] MIN,BOTH OVER 1.27μm[.000050] MIN NICKEL.

0.76μm[.000030] MIN PRECIOUS METAL PLATE FOR A LENGTH OF 7.62[.300] MIN FROM MATING END, 3.81μm[.000150] MIN TIN ON OPPOSITE END FOR A LENGTH OF 5.08[.200] MIN, BOTH OVER 1.27μm[.000050] MIN NICKEL.

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	6.60 [.260]	4	213788-3
	6.60 [.260]	3	213788-2
	17.53 [.690]	1	213788-1
SUPERSEDED BY 213788-2	A	CONTACT FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.OBERMAN 1-5-94	 TE Connectivity				
DIMENSIONS: mm [INCHES]		CHK R.STONE 1-7-94					
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 P.LC ± - 1 P.LC ± - 2 P.LC ± 0.25 [010] 3 P.LC ± - 4 P.LC ± - ANGLES ± - FINISH -	NAME	HEADER ASSEMBLY, 62 POSN, ACTION PIN TM				
		PRODUCT SPEC	-				
		APPLICATION SPEC	-				
		WEIGHT	-				
		CUSTOMER DRAWING	-				
		MATERIAL	FINISH	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
				A1	00779	C213788	-
		SCALE	2:1	SHEET	1 OF 1		
		REV G					