




LOC		DIST		REVISIONS				
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD	
		A		CREATED BY AUTOMATION PROGRAM	02MAY2011	RKC	JE	
		A1		REVISED PER ECN-24-252036	25MAR2024	AP	RS	





- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30µ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30µ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.



252X Ø0.39±0.05
PLATED THRU HOLE
Ø0.10

UNGUIDED
BACKPLANE HOLE PATTERN
(CONNECTOR SIDE)




THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	R. COELLO	02MAY2011	TE Connectivity IMPACT, 6 PAIR, 14 COLUMN, HEADER UNGUIDED, DUAL END WALL SIGNAL MODULE, 0.39 PTH			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	J. EABY	02MAY2011				
mm		0 PLC ±		APVD	J. EABY	02MAY2011				
		1 PLC ±0.25		PRODUCT SPEC		NAME				
		2 PLC ±0.13		APPLICATION SPEC		SIZE		CAGE CODE		
		3 PLC ±		WEIGHT		DRAWING NO		RESTRICTED TO		
MATERIAL		ANGLES		FINISH		A100779		C=2132014		
		SEE TABLE		CUSTOMER DRAWING		SCALE		5:1		
						SHEET		1 OF 2		
						REV		A1		

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-

	5.5	2132014-6	OBSOLETE
	4.9	2132014-5	
	4.5	2132014-4	
	5.5	2132014-3	
	4.9	2132014-2	
	4.5	2132014-1	
FINISH	DIM M	PART NUMBER	

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN R. COELLO	02MAY2011	 TE Connectivity		
DIMENSIONS:			CHK J. EABY	02MAY2011			
mm			APVD J. EABY	02MAY2011	NAME IMPACT, 6 PAIR, 14 COLUMN, HEADER UNGUIDED, DUAL END WALL SIGNAL MODULE, 0.39 PTH		
			TOLERANCES UNLESS OTHERWISE SPECIFIED:				
			0 PLC ± 0.25				
			1 PLC ± 0.13				
			2 PLC ± 0.13				
			3 PLC ± 0.13				
			APPLICATION SPEC		SIZE A1		
			APPLICATION SPEC				
MATERIAL			WEIGHT		CAGE CODE 00779		
FINISH			SEE TABLE		DRAWING NO 2132014		
					RESTRICTED TO -		
CUSTOMER DRAWING					SCALE	5:1	
					SHEET	2 OF 2	
					REV	A1	