



LOC		DIST		REVISIONS					
P	LYR	DESCRIPTION				DATE	DWN	APVD	
	I	DRAWING CREATED BY AUTOMATION PROGRAM				05JAN2011	-	JE	
	A	RELEASED				29FEB2012	BC	DY	
	A1	REVISED PER ECN-24-252171				08MAR2024	AP	RS	

- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.
4. SCREWS PACKAGED IN END OF PACKAGING TUBE.
- 5 FOR GROUNDED GUIDE PIN USE Ø3.56±0.08 PTH,
Ø3.66 DRILL, AND Ø6.5 PAD.
6. KEYING PIN SHOWN IN POSITION A, SEE KEYING CHART
ON SHEET 2 FOR OTHER POSITIONS.

NOTCH DESIGNATES
ROW A



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	05JAN2011	TE Connectivity	
DIMENSIONS:		CHK	05JAN2011		
mm		APVD	05JAN2011		
		PRODUCT SPEC			
		APPLICATION SPEC		NAME IMPACT, 3 PAIR, 6 COLUMN, HEADER RIGHT GUIDED, OPEN END WALL SIGNAL MODULE, 0.39 PTH	
		FINISH	SEE TABLE		
MATERIAL		WEIGHT	-	SIZE	CAGE CODE
		CUSTOMER DRAWING		A1	00779
		SCALE	6:1	SHEET	1 OF 2
		REV	A1		

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-	SEE SHEET 1	-	-	-	

	H	5.5	8-2132531-6	OBSOLETE
	H	4.9	8-2132531-5	
	H	4.5	8-2132531-4	
	H	5.5	8-2132531-3	
	H	4.9	8-2132531-2	
	H	4.5	8-2132531-1	
	G	5.5	7-2132531-6	
	G	4.9	7-2132531-5	
	G	4.5	7-2132531-4	
	G	5.5	7-2132531-3	
	G	4.9	7-2132531-2	
	G	4.5	7-2132531-1	
	F	5.5	6-2132531-6	
	F	4.9	6-2132531-5	
	F	4.5	6-2132531-4	
	F	5.5	6-2132531-3	
	F	4.9	6-2132531-2	
	F	4.5	6-2132531-1	
	E	5.5	5-2132531-6	
	E	4.9	5-2132531-5	
	E	4.5	5-2132531-4	
	E	5.5	5-2132531-3	
	E	4.9	5-2132531-2	
	E	4.5	5-2132531-1	
	D	5.5	4-2132531-6	
	D	4.9	4-2132531-5	
	D	4.5	4-2132531-4	
	D	5.5	4-2132531-3	
	D	4.9	4-2132531-2	
	D	4.5	4-2132531-1	
	C	5.5	3-2132531-6	
	C	4.9	3-2132531-5	
	C	4.5	3-2132531-4	
	C	5.5	3-2132531-3	
	C	4.9	3-2132531-2	
	C	4.5	3-2132531-1	
	B	5.5	2-2132531-6	
	B	4.9	2-2132531-5	
	B	4.5	2-2132531-4	
	B	5.5	2-2132531-3	
	B	4.9	2-2132531-2	
	B	4.5	2-2132531-1	
	A	5.5	1-2132531-6	OBSOLETE
	A	4.9	1-2132531-5	
	A	4.5	1-2132531-4	
	A	5.5	1-2132531-3	
	A	4.9	1-2132531-2	OBSOLETE
	A	4.5	1-2132531-1	
	-	5.5	2132531-6	
	-	4.9	2132531-5	
	-	4.5	2132531-4	OBSOLETE
	-	5.5	2132531-3	
	-	4.9	2132531-2	
	-	4.5	2132531-1	
FINISH	KEY POSITION	DIM M	PART NUMBER	

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

KEY POSITION
CHART

NONE

A

E

B

F

C

G

D

H

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	05JAN2011	TE Connectivity	
		CHK	05JAN2011		
		J. EABY	05JAN2011		
DIMENSIONS:		APVD	J. EABY	NAME	IMPACT, 3 PAIR, 6 COLUMN, HEADER
mm		PRODUCT SPEC		RIGHT GUIDED, OPEN END WALL	
		APPLICATION SPEC		SIGNAL MODULE, 0.39 PTH	
MATERIAL		WEIGHT	-	SIZE	CAGE CODE
-		CUSTOMER DRAWING		DRAWING NO	RESTRICTED TO
				A100779C=2132531	-
				SCALE	SHEET
				5:1	2 OF 2
				REV	A1