





P.C.B. LAYOUT  FIG. 1
(GENERAL TOLERANCE ±0.1)

NOTES;
1. GENERAL TOLERANCE: ±0.3
2. APPLICABLE PCB THICKNESS 1.6mm
3. MATING CONN. P/N
PLUG HOUSING (66 NYLON GLASS FILLED);
P/N x-1747066-5 (5POS)
4. APPLICABLE PCB LAYOUT SEE FIG.1
 5. APPLICABLE PCB HOLE DIA. (ø D)
PUNCHED HOLE: 0.7 ^{+0.1}/₀ mm
DRILLED HOLE: 0.9±0.05mm

TABLE 1

②	HEADER HOUSING	66NYLON GLASS FILLED
①	POST CONTACT	Au PLATED COPPER ALLOY
P/N	PART NAME	MATERIAL & FINISH

NATURAL	2134442-1
COLOR	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.KUDO 02JUL2010	 Tyco Electronics Corporation Kawasaki, Japan			
DIMENSIONS: mm		CHK N.YAMASAKI 02JUL2010				
		APVD T.MASUDA 02JUL2010	NAME GRACE INERTIA CONNECTOR 2.5 HEADER ASSEMBLY (H-TYPE) 5 POS Au PLATING			
		PRODUCT SPEC				
MATERIAL SEE TABLE1		FINISH	APPLICATION SPEC	SIZE A3		
			WEIGHT	CAGE CODE 00779	DRAWING NO C=2134442	RESTRICTED TO
CUSTOMER DRAWING			SCALE 3:1	SHEET 1 OF 1	REV A	