


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G	REVISED PER ECR-24-213594	02JUL2024	RK	FJS



- 1 STAINLESS STEEL.
- 2 BRASS.
- 3 1.27μm [.000050] MIN TIN-LEAD OVER 1.27μm [.000050] MIN NICKEL.
- 4 WIRE RANGE: 14-18 AWG. INSULATION RANGE: 2.79-3.81 [.110-.150] DIA.
- 5 0.76μm [.000030] MIN PRECIOUS METAL PLATE IN LOCALIZED GOLD PLATE AREA, OVER 1.27μm [.000050] MIN NICKEL.
- 6 1.27μm [.000050] MIN TIN OVER 1.27μm [.000050] MIN NICKEL.
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	LOOSE PIECE	6	213603-6
	STRIP	6	213603-5
7	OBSOLETE LOOSE PIECE	5	-213603-4-
	STRIP	5	213603-3
OBSOLETE	LOOSE PIECE	3	-213603-2-
	STRIP	3	213603-1
	DESCRIPTION	PIN FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.SIPE 05/07/90	TE Connectivity		
		CHK R STONE 5-17-90			
DIMENSIONS: mm [INCHES]		APVD -	NAME PIN ASSEMBLY, 5015 SERIES, 14-18 AWG, SPECIAL TYPE III+		
		PRODUCT SPEC -			
		APPLICATION SPEC -			
		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-213603
MATERIAL SPRING: 1 PIN: 2		FINISH SEE TABLE	RESTRICTED TO -		
			CUSTOMER DRAWING		
			SCALE 4:1	SHEET 1 OF 1	REV G