






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
D		REVISED PER ECR-24-213594	05JUL2024	RK	FJS



PART NO & DATE CODE MARKED IN AREA INDICATED, ON EITHER SIDE



REAR MOUNTED PANEL CUTOUT
SCALE 1:1



FRONT MOUNTED PANEL CUTOUT
SCALE 1:1

- 1 CAVITY IDENTIFICATION CHARACTERS ON FRONT AND REAR FACE.
- 2 NYLON, UL 94V-O RATED, BLACK.
- 3 CONTACT BODY: 0.76um[.000030] MIN PRECIOUS METAL PLATE FOR A LENGTH OF 5.08[.200] MIN FROM MATING END, GOLD FLASH ON REMAINDER, BOTH OVER 1.27um [.000050] MIN NICKEL.
- 4 CONTACT POST: 2.54um[.000100] MIN TIN-LEAD OVER 2.54um[.000100] MIN COPPER.
- 5 CONTACT POST: 2.54um[.000100] MIN TIN OVER 2.54um[.000100] MIN COPPER.
- 6 SHELL: 5.08um[.000200] MIN NICKEL OVER 10.16um[.000400] MIN COPPER.
- 7 NO CONTACTS IN POSITION 10 AND 11.

7	OBsolete	5	213734-3
		6	213734-2
		4	213734-1
		POST FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. OBERMAN 1-6-92	TE Connectivity	
		CHK R. STONE 1-8-92		
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	NAME	RESTRICTED TO
	0 PLC ± -	PRODUCT SPEC	RECEPTACLE ASSEMBLY, 22-16, STD SEX, CMC	-
	1 PLC ± -	APPLICATION SPEC		
	2 PLC ± 0.13 [.005]			
	3 PLC ± -			
MATERIAL -	FINISH -	WEIGHT 0.000000	SIZE A1 CAGE CODE 00779 DRAWING NO 213734	REV D
CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 1	